



CWPT wraparound repair sleeve heat shrink kit, unpresurized, for 8 to 45 mm cable diameter, 250 mm long

- Excellent split resistance of the composite structure offers superior resistance to mechanical abuse during and after the installation
- Integrated moisture barrier completely reconstitutes the cable sheath construction

## OBSOLETE

This product was discontinued on: June 30, 2022

## Product Classification

|                              |                           |
|------------------------------|---------------------------|
| <b>Regional Availability</b> | EMEA                      |
| <b>Product Type</b>          | Heat shrink repair sleeve |
| <b>Product Series</b>        | CWPT                      |

## General Specifications

|                     |                  |
|---------------------|------------------|
| <b>Color</b>        | Black            |
| <b>Sealant Type</b> | Hotmelt adhesive |

## Dimensions

|                                           |                   |
|-------------------------------------------|-------------------|
| <b>Length</b>                             | 250 mm   9.843 in |
| <b>Expanded Inside Diameter, minimum</b>  | 45 mm   1.772 in  |
| <b>Recovered Inside Diameter, maximum</b> | 8 mm   0.315 in   |
| <b>Single Cable Diameter, maximum</b>     | 45 mm   1.772 in  |
| <b>Single Cable Diameter, minimum</b>     | 8 mm   0.315 in   |
| <b>Expanded Wall Thickness, minimum</b>   | 1.1 mm   0.043 in |

## Material Specifications

|                      |                                             |
|----------------------|---------------------------------------------|
| <b>Material Type</b> | Fiber-reinforced multi-layer sealing sleeve |
|----------------------|---------------------------------------------|

## Environmental Specifications

**Environmental Space**

Aerial | Buried | Ducted

## Packaging and Weights

**Packaging quantity**

1

**Packaging Type**

Bag | Carton

## Regulatory Compliance/Certifications

**Agency****Classification**

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

