

CS41CM, ETL Verified Category 6A U/UTP Cable, non-plenum, white jacket, 4 pair count, 1000 ft (305 m) length reel

Product Classification

Regional Availability

Asia | Australia/New Zealand

Portfolio NETCONNECT®

Product Type Twisted pair cable

General Specifications

Product Number CS41CM

ANSI/TIA Category 6A

Cable Component Type Horizontal

Cable Type U/UTP (unshielded)

Conductor Type, singles Solid
Conductors, quantity 8

Jacket Color White

Pairs, quantity 4

Separator Type Isolator

Transmission Standards ANSI/TIA-568.2-D | IEC 61156-5

Dimensions

Cable Length 304.8 m | 1000 ft


Diameter Over Insulated Conductor1.113 mm | 0.044 inDiameter Over Jacket, nominal7.087 mm | 0.279 in

Jacket Thickness 0.508 mm | 0.02 in

Conductor Gauge, singles 23 AWG

Cross Section Drawing





Electrical Specifications

dc Resistance Unbalance, maximum 4 %

dc Resistance, maximum 8 ohms/100 m | 2.438 ohms/100 ft

Delay Skew, maximum 45 ns

Dielectric Strength, minimum1500 Vac | 2500 VdcMutual Capacitance at Frequency5.6 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 67 %

Remote Powering Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the

safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2,

CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Safety Voltage Rating 300 V



Flectrical Cable Performance

CS CommScope

STD Refers to the standard value listed under Transmission Standards in the Electrical Specifications above

TYP Typical Electrical Performance

IL Insertion Loss (dB/100m) NEXT Near End Crosstalk (dB/100m)

 ACR
 Attenuation to Crosstalk Ratio (dB/100m)
 PSNEXT
 Power Sum Near End Crosstalk (db/100m)

 PSACR
 Power Sum Attenuation to Crosstalk Ratio (dB/100m)
 ACRF
 Attenuation to Crosstalk Ratio - Far End (dB/100m)

PSACRF Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m) RL Return Loss (dB)

TCL Transverse Conversion Loss (dB/100m) ELTCTL Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL STD	NEXT STD	ACR STD	PSNEXT STD	PSACR STD	ACRF STD	PSACRF STD	RL STD
4	3.8	66.3	62.5	63.3	59.5	55.9	53	23
8	5.3	61.7	56.4	58.7	53.4	49.9	46.9	24.5
10	5.9	60.3	54.4	57.3	51.4	48	45	25
16	7.5	57.2	49.7	54.2	46.7	43.9	40.9	25
20	8.4	55.8	47.4	52.8	44.4	42	39	25
25	9.4	54.3	44.9	51.3	41.9	40	37	24.3
31.25	10.5	52.9	42.4	49.9	39.4	38.1	35.1	23.6
62.5	15	48.4	33.4	45.4	30.4	32.1	29.1	21.5
100	19.1	45.3	26.2	42.3	23.2	28	25	20.1
155	24.1	42.4	18.3	39.4	15.3	24.2	21.2	18.8
200	27.6	40.8	13.2	37.8	10.2	22	19	18
250	31.1	39.3	8.3	36.3	5.3	20	17	17.3
300	34.3	38.1	3.9	35.1	0.9	18.4	15.5	16.8
350	37.2	37.1	-0.1	34.1	-3.1	17.1	14.1	16.3
400	40.1	36.3	-3.8	33.3	-6.8	15.9	13	15.9
500	45.3	34.8	-10.5	31.8	-13.5	14	11	15.2

Material Specifications

Conductor Material Bare copper

Insulation Material Polyolefin

Jacket Material PVC

Separator Material Polyolefin

Tape Material Poly/Aluminum/Poly

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications



Installation temperature $0 \, ^{\circ}\text{C} \text{ to } +60 \, ^{\circ}\text{C} \text{ (+32 } ^{\circ}\text{F to } +140 \, ^{\circ}\text{F)}$

Operating Temperature $-20 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Environmental Space Non-plenum

Flame Test Method CM | NEC Article 800 | UL 1685 | UL 910

Packaging and Weights

Cable weight 46.297 kg/km | 31.11 lb/kft

Packaging Type Reel

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

