

### Butterfly Hanger for 1-1/4 in coaxial cable and elliptical waveguide 64

#### **Product Classification**

Product Type Hanger kit

Ordering Note CommScope® non-standard product

General Specifications

Cables per Hanger 1

**Color** Silver

**Hanger Type** Standard butterfly hanger

Mounting 3/8 in (M10) drilled cable ladder

**Dimensions** 

Maximum Stack Height 0

**Height** 58.9 mm | 2.319 in

**Width** 38.1 mm | 1.5 in

**Length** 76.2 mm | 3 in

**Compatible Cable Diameter Range** 37.6–43.2 mm

Compatible Diameter, maximum 43.2 mm | 1.701 in

**Compatible Diameter, minimum** 37.6 mm | 1.48 in

Nominal Size 1-1/4 in

**Electrical Specifications** 

Return Loss Effect, maximum0.1 dBDTF Effect, maximum0.1 dB

Material Specifications

Material Type Stainless steel

Mechanical Specifications



# 42396A-1

#### **Vibration Survival**

≥4 hours at resonant frequency

## **Environmental Specifications**

Operating Temperature  $-40 \,^{\circ}\text{C}$  to  $+85 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to  $+185 \,^{\circ}\text{F}$ )

**Corrosion Resistance, minimum with no degredation** ≥500 hours in salt spray chamber

**Environmental Strength Capability**Double cable weight

Packaging and Weights

 Height, packed
 26 cm | 10.236 in

 Width, packed
 9 cm | 3.543 in

 Length, packed
 9 cm | 3.543 in

Packaging quantity 10

**Weight, gross** 0.53 kg | 1.168 lb

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



## \* Footnotes

Maximum Stack Height Fiber, Hybrid, Power

