

DHK-12-6-P



Double Hanger Kit for 1/2 in coaxial cable, triple stack; includes hardware and angle adapter

Product Classification

Product Type	Hanger kit
Product Brand	ValuSite™
Ordering Note	CommScope® non-standard product

General Specifications

Cables per Hanger	6
Color	Black
Hanger Type	Composite clamp
Mounting	M8 hardware

Dimensions

Maximum Stack Height	3
Height	78 mm 3.071 in
Width	25.9 mm 1.02 in
Length	66 mm 2.598 in
Compatible Cable Diameter Range	15.2–16.3 mm
Compatible Diameter, maximum	16.3 mm 0.642 in
Compatible Diameter, minimum	15.2 mm 0.598 in
Nominal Size	1/2 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Engineered plastic Stainless steel 304
----------------------	--

DHK-12-6-P

Mechanical Specifications

Vibration Survival

≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature

-40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation

≥500 hours in salt spray chamber

Environmental Strength Capability

Double cable weight

UV Resistance, minimum with no degradation

≥100 hours exposure in accelerated UV life chamber

Packaging and Weights

Height, packed

30.4 cm | 11.969 in

Width, packed

27.9 cm | 10.984 in

Length, packed

2.5 cm | 0.984 in

Included

Angle adapter | Hardware

Packaging quantity

1

Weight, gross

0.46 kg | 1.014 lb

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power