
MT-357-12



Trapeze Kit, 12 in wide, one rung

Product Classification

Product Type Trapeze kit

General Specifications

Application Waveguide bridge kit, 12 in

Cable Runs, quantity 7
Hole, quantity 7

Mounting Waveguide bridge channel

Rungs, quantity 1

Dimensions


 Height
 50.8 mm | 2 in

 Width
 355.6 mm | 14 in

 Length
 152.4 mm | 6 in

 Hole Size
 3/4 in | 7/16 in

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Hardware | Threaded rod | Z-bracket

Packaging quantity 1

Weight, net 1.8 kg | 3.968 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ANDREW® an Amphenol company

MT-357-12

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted




Included Products

ZB-H4 - Horizontal Z-bracket, 11 in, for seven coaxial cable

runs



7B-H4



Horizontal Z-bracket, 11 in, for seven coaxial cable runs

Product Classification

Product Type Z-Bracket

Ordering Note ANDREW® standard product (Global)

General Specifications

Cable Runs, quantity 7

Hole, quantity 7

Mounting Walls

Dimensions

 Height
 50.8 mm | 2 in


 Width
 152.4 mm | 6 in

 Length
 279.4 mm | 11 in

 Hole Size
 3/4 in | 7/16 in

ZB-H4

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Packaging and Weights

Included Z-bracket

Packaging quantity 1

Weight, net 1.2 kg | 2.646 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

ANDREW® an Amphenol company

ZB-H4



* Footnotes

Wind Rating

BWS-Base Wind Speed; FBC-Florida Building Code

