

RM-DM-6



Dual Ring Mount kit for 6 ft Microwave Antenna

Product Classification

Product Type Universal ring mount

General Specifications

Mounting Monopole, 254–1270 mm (10–50 in) OD

Pipe, quantity 1

Sectors, quantity 1

Dimensions

Height 254 mm | 10 in

Width 736.6 mm | 29 in

Length 1,600.2 mm | 63 in

Pipe Length 1,600.2 mm | 63 in

Mounting Diameter, maximum 1270 mm | 50 in

Mounting Diameter, minimum 381 mm | 15 in

Pipe Outer Diameter 114.3 mm | 4.5 in

Mounting Circumference, maximum 3,990.34 mm | 157.1 in

Mounting Circumference, minimum 1,196.34 mm | 47.1 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Hardware | Mount | Pipe

Packaging quantity 1

Weight, net 178.8 kg | 394.186 lb

RM-DM-6

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

