
760250070 | C-048-LA-5L-M12BK/25G/GY/FS



Fiber indoor/outdoor cable, LazrSPEED®, Single Jacket/Single Armor, 90 min Fire Survival, Low Smoke Zero Halogen (LSZH), 48 fiber, Gel-Filled, Stranded Loose Tube, Multimode OM3, Black jacket color, Meters cable marking

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-LA

General Specifications

Armor Type Corrugated steel

Cable Type Stranded loose tube

Construction TypeArmoredSubunit TypeGel-filled

Filler, quantity 2

Jacket Color Black

Jacket Marking Method Inkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE 760250070 48x50/125 0M3 ULSZH [Serial number]

[metre mark]

Subunit, quantity 4
Fibers per Subunit, quantity 12
Total Fiber Count 48


Dimensions

Buffer Tube/Subunit Diameter2.5 mm0.098 inDiameter Over Jacket14 mm0.551 in



760250070 | C-048-LA-5L-M12BK/25G/GY/FS

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded330 mm | 12.992 inMinimum Bend Radius, unloaded200 mm | 7.874 inTensile Load, long term, maximum1200 N | 269.771 lbfTensile Load, short term, maximum4000 N | 899.236 lbfCompression20 N/mm | 114.203 lb/in

•

Impact 5 N-m | 44.254 in lb

Impact Test Method IEC 60794-1 E4

Strain See long and short term tensile loads

IEC 60794-1 E3

Strain Test Method IEC 60794-1 E1

Twist 5 cycles

Twist Test Method IEC 60794-1 E7

Optical Specifications

Compression Test Method

Fiber Type OM3 | OM3, LazrSPEED® 300

Environmental Specifications

Operating Temperature $-30 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-22 °F to +158 °F)Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Page 2 of 3



760250070 | C-048-LA-5L-M12BK/25G/GY/FS

Cable Qualification Standards EN 187105 | IEC 60794-1-2

Environmental Space Aerial, lashed | Buried | Low Smoke Zero Halogen (LSZH)

Flame Test Method | IEC 60331-25 | IEC 60332-1 | IEC 60332-3-24 | IEC 60754-1 | IEC 60754-

2 | IEC 61034-2 | NES 713 (<=5 - jacket material only)

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method IEC 60794-1 F5

Environmental Test Specifications

Low High Bend Test Method IEC 60794-1 E11

Temperature Cycle -20 °C to +70 °C (-4 °F to +158 °F)

Temperature Cycle Test Method IEC 60794-1 F1

Packaging and Weights

Cable weight 240 kg/km | 161.273 lb/kft

Included Products

CS-5L-LT - LazrSPEED® 300 OM3 Bend-Insensitive Multimode

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

