MDC-JJ1G



RealFlex® 3 Fiber Optic Drop Cable Assembly, SC/APC to SC/APC, RBR Plenum, Ivory

- Allow for a fiber bend radius as small as 7.5 millimeters without changing attenuation characteristics, and improve the insertion loss (IL) performance for 90-degree bend locations
- Indoor/outdoor cable available in both riser and plenum cable types for use in residential, business or MDU (multiple dwelling unit) structures

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber drop cable assembly

Product Brand RealFlex®

Product Series MDC

Ordering NoteLengths 1-350 ft are coiled. Lengths 351 ft + are spooled. Lengths under 351' that

require a spool will need to include a spool option J at the end of the MID. When "J"

option is included in the MID then Connector A will deploy first.

General Specifications

Cable Type Stapleable - Round

Connector A, quantity 1

Color, boot A Green
Color, connector A Green

Connector B, quantity

 Color, boot B
 Green

 Color, connector B
 Green

 Interface, Connector A
 SC/APC

 Interface Feature, connector A
 Male

 Interface, Connector B
 SC/APC

Interface Feature, connector B Male

Jacket Color Ivory

Total Fibers, quantity 1

Transmission Standards TIA/EIA-568-B.3



MDC-JJ1G


Dimensions

Cable Assembly Length Range (m) 1 - 305

Cable Assembly Length Range (ft) 1 - 1000

Cable Outer Diameter 2.9 mm (0.11 in)

Ordering Tree



^{*}Drops are automatically coiled 0-350 ft. Lengths 351+are automatically spooled. Connector A deploys first. Add

Mechanical Specifications

Minimum Bend Radius, loaded 50 mm | 1.969 in Minimum Bend Radius, unloaded 30 mm | 1.181 in

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A2/B2

Insertion Loss, maximum, connector A0.4 dBInsertion Loss, maximum, connector B0.4 dBReturn Loss, minimum, connector A65 dB

COMMSCOPE®

option J if spool is required for lengths 350ft or less.
**Cable length shown as an example; additional cable lengths available upon request up to 1500 ft

MDC-JJ1G

Return Loss, minimum, connector B 65 dB

Environmental Specifications

Installation temperature $-20 \,^{\circ}\text{C to} + 60 \,^{\circ}\text{C (-4 °F to} + 140 \,^{\circ}\text{F)}$ Operating Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (-40 °F to} + 158 \,^{\circ}\text{F)}$

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +75 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +167 \,^{\circ}\text{F})$

Environmental Space Plenum

Flame Test Listing FT6 | NEC OFNP (UL) and c(UL)

Flame Test Method C22.2 | NFPA 262

Jacket UV Resistance UV stabilized

Qualification Standards GR-409

Packaging and Weights

Cable weight 7.9 kg/km | 5.309 lb/kft

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

