
810009944/DB | S-096-LN-8W-M12NS/25G/S



Fiber OSP cable, LightScope® ZWP All-Dielectric Self-Supporting, 96 fiber, 2.5mm Gel-filled Tubes, Singlemode G.652.D and G.657.Al, Meters jacket marking

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber OSP cable

Product Series S-LN

General Specifications

Cable Type Stranded loose tube

Construction Type Non-armored

Subunit Type Gel-filled

Filler, quantity 0

Jacket Color Black

Jacket Marking Meters

Subunit, quantity 8

Fibers per Subunit, quantity 12

Total Fiber Count 96

Dimensions


Buffer Tube/Subunit Diameter 2.5 mm | 0.098 in

Diameter Over Jacket 12.72 mm | 0.501 in

Representative Image



810009944/DB | S-096-LN-8W-M12NS/25G/S



Material Specifications

Jacket Material PE

Mechanical Specifications

Minimum Bend Radius, loaded 191 mm | 7.52 in Minimum Bend Radius, unloaded 127 mm | 5 in

Tensile Load, long and short termSee Sag and Tension tables in Product Documentation section

 Compression
 22 N/mm | 125.623 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

 Impact
 2.94 N-m | 26.021 in lb

 Impact Test Method
 FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Optical Specifications

Fiber Type G.652.D and G.657.A1 | G.652.D and G.657.A1

Environmental Specifications

Installation temperature -30 °C to +70 °C (-22 °F to +158 °F)

Page 2 of 3



810009944/DB | S-096-LN-8W-M12NS/25G/S

Operating Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature

-40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification Standards

ANSI/ICEA S-87-640 | IEEE-1222

Environmental Space Aerial, self-support

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze-2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Drip 80 °C | 176 °F

Drip Test Method FOTP-81 | IEC 60794-1 E14

Heat Age $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 111 kg/km | 74.589 lb/kft

Included Products

DB-8W-LT - LightScope® ZWP Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

