

# AVA6RKP-50-35



AVA6RK-50, HELIAX® Andrew Virtual Air™ Premium Coaxial Cable, corrugated copper, 1-1/4 in, black, fire retardant polyolefin jacket B2ca-s1b, d2,a1 (CPR testing is conducted annually please reference the website for latest classification)

## Product Classification

<b>Product Type</b>	Coaxial wireless cable
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	AVA6-50

## General Specifications

<b>Product Number</b>	520092202/00
<b>Flexibility</b>	Standard
<b>Jacket Color</b>	Black
<b>Performance Note</b>	Attenuation values typical, guaranteed within 5%

## Dimensions

<b>Diameter Over Dielectric</b>	34.036 mm   1.34 in
<b>Diameter Over Jacket</b>	39.624 mm   1.56 in
<b>Inner Conductor OD</b>	14.021 mm   0.552 in
<b>Outer Conductor OD</b>	36.068 mm   1.42 in
<b>Nominal Size</b>	1-1/4 in

## Electrical Specifications

<b>Cable Impedance</b>	50 ohm ±1 ohm
<b>Capacitance</b>	72 pF/m   21.946 pF/ft
<b>dc Resistance, Inner Conductor</b>	1.74 ohms/km   0.53 ohms/kft
<b>dc Resistance, Outer Conductor</b>	0.75 ohms/km   0.229 ohms/kft
<b>dc Test Voltage</b>	8500 V
<b>Inductance</b>	0.187 µH/m   0.057 µH/ft
<b>Insulation Resistance</b>	100000 MOhms-km
<b>Jacket Spark Test Voltage (rms)</b>	10000 V
<b>Operating Frequency Band</b>	1 – 4000 MHz

# AVA6RKP-50-35

---

<b>Peak Power</b>	180 kW
<b>Velocity</b>	92 %

## VSWR/Return Loss

<b>Frequency Band</b>	<b>VSWR</b>	<b>Return Loss (dB)</b>
703–803 MHz	1.201	20.8
885–960 MHz	1.151	23.1
1710–2170 MHz	1.151	23.1
2490–2690 MHz	1.201	20.8
3300–3400 MHz	1.433	15
3400–3700 MHz	1.25	19.1
3700–3800 MHz	1.433	15
3800–4000 MHz	1.377	16

## Attenuation

<b>Frequency (MHz)</b>	<b>Attenuation (dB/100 m)</b>	<b>Attenuation (dB/100 ft)</b>	<b>Average Power (kW)</b>
1.0	0.079	0.024	82.63
1.5	0.097	0.03	67.41
2.0	0.113	0.034	58.33
10.0	0.253	0.077	25.89
20.0	0.36	0.11	18.21
30.0	0.443	0.135	14.8
50.0	0.576	0.176	11.39
85.0	0.758	0.231	8.66
88.0	0.772	0.235	8.51
100.0	0.825	0.251	7.96
108.0	0.858	0.262	7.65
150.0	1.019	0.311	6.44
174.0	1.102	0.336	5.96
200.0	1.186	0.361	5.53
204.0	1.198	0.365	5.48
300.0	1.471	0.448	4.46
400.0	1.717	0.523	3.82
450.0	1.829	0.558	3.59
460.0	1.851	0.564	3.54

# AVA6RKP-50-35

---

500.0	1.937	0.59	3.39
512.0	1.962	0.598	3.34
600.0	2.14	0.652	3.07
700.0	2.329	0.71	2.82
800.0	2.507	0.764	2.62
824.0	2.548	0.777	2.58
894.0	2.666	0.813	2.46
960.0	2.774	0.846	2.37
1000.0	2.838	0.865	2.31
1218.0	3.171	0.967	2.07
1250.0	3.218	0.981	2.04
1500.0	3.569	1.088	1.84
1700.0	3.835	1.169	1.71
1794.0	3.955	1.206	1.66
1800.0	3.963	1.208	1.66
2000.0	4.212	1.284	1.56
2100.0	4.333	1.321	1.51
2200.0	4.452	1.357	1.47
2300.0	4.569	1.393	1.44
2500.0	4.798	1.462	1.37
2700.0	5.021	1.53	1.31
3000.0	5.345	1.629	1.23
3400.0	5.76	1.755	1.14
3600.0	5.961	1.817	1.1
3700.0	6.06	1.847	1.08
3800.0	6.16	1.877	1.07
4000.0	6.36	1.94	1.03

## Material Specifications

<b>Dielectric Material</b>	Foam PE
<b>Jacket Material</b>	Non-halogenated, fire retardant polyolefin
<b>Inner Conductor Material</b>	Corrugated copper tube
<b>Outer Conductor Material</b>	Corrugated copper

## Mechanical Specifications

<b>Minimum Bend Radius, multiple Bends</b>	203.2 mm   8 in
--	-----------------

# AVA6RKP-50-35

---

<b>Minimum Bend Radius, single Bend</b>	152.4 mm   6 in
<b>Number of Bends, minimum</b>	15
<b>Number of Bends, typical</b>	40
<b>Tensile Strength</b>	154 kg   339.511 lb
<b>Bending Moment</b>	29.8 N-m   263.752 in lb
<b>Flat Plate Crush Strength</b>	1.3 kg/mm   72.797 lb/in

## Environmental Specifications

<b>Installation temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Operating Temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Storage Temperature</b>	-40 °C to +60 °C (-40 °F to +140 °F)
<b>Attenuation, Ambient Temperature</b>	68 °F   20 °C
<b>Average Power, Ambient Temperature</b>	104 °F   40 °C
<b>Average Power, Inner Conductor Temperature</b>	212 °F   100 °C
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	B2ca
<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s1b
<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d2
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a1
<b>Fire Retardancy Test Method</b>	IEC 60332-1-2   NFPA 130-2010   UL 1666/CATVR
<b>Smoke Index Test Method</b>	IEC 61034
<b>Toxicity Index Test Method</b>	IEC 60754-1   IEC 60754-2

## Packaging and Weights

<b>Cable weight</b>	0.8 kg/m   0.538 lb/ft
---------------------	------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

# AVA6RKP-50-35

---

