



Fiber Indoor/Outdoor cable, TeraSPEED®, 120 min Fire Survival, Low Smoke Zero Halogen (LSZH), 4 fiber, Gel-Filled, Central Loose Tube, Singlemode G.652.D and G.657.A1, Meters jacket marking, Black jacket color. Provides Rodent Resistance.

## Product Classification

|                              |                                     |
|------------------------------|-------------------------------------|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA |
| <b>Portfolio</b>             | CommScope®                          |
| <b>Product Type</b>          | Fiber indoor/outdoor cable          |
| <b>Product Series</b>        | C-L2                                |

## General Specifications

|                                     |   |
|-------------------------------------|---|
| <b>Armor Type</b>                   | Corrugated steel  |
| <b>Cable Type</b>                   | Loose tube  |
| <b>Subunit Type</b>                 | Gel-filled  |
| <b>Jacket Color</b>                 | Black   |
| <b>Jacket Marking</b>               | Meters  |
| <b>Jacket Marking Method</b>        | Inkjet  |
| <b>Jacket Marking Text</b>          | COMMSCOPE GB SYSTEM F.O. CABLE X-1716219-4 INT/EXT FIRE SURVIVAL 4 X 9/125 OS2 [Serial NUMBER] [METRE MARK] |
| <b>Fibers per Subunit, quantity</b> | 4   |
| <b>Total Fiber Count</b>            | 4   |

## Dimensions

|                                     |                  |
|-------------------------------------|------------------|
| <b>Buffer Tube/Subunit Diameter</b> | 4 mm   0.157 in  |
| <b>Diameter Over Jacket</b>         | 12.7 mm   0.5 in |

## Mechanical Specifications

|  |                      |
|--|----------------------|
| <b>Minimum Bend Radius, loaded</b>       | 330 mm   12.992 in   |
| <b>Minimum Bend Radius, unloaded</b>     | 255 mm   10.039 in   |
| <b>Tensile Load, long term, maximum</b>  | 400 N   89.924 lbf   |
| <b>Tensile Load, short term, maximum</b> | 1400 N   314.733 lbf |

# 2-1716219-4 | C-004-L2-8W-M04BK/40G/GY/FS /B

|                                |                                       |
|--------------------------------|---------------------------------------|
| <b>Compression</b>             | 30 N/mm   171.304 lb/in               |
| <b>Compression Test Method</b> | IEC 60794-1 E3                        |
| <b>Impact</b>                  | 10 N-m   88.507 in lb                 |
| <b>Impact Test Method</b>      | IEC 60794-1 E4                        |
| <b>Strain</b>                  | See long and short term tensile loads |
| <b>Strain Test Method</b>      | IEC 60794-1 E1                        |
| <b>Twist</b>                   | 5 cycles                              |
| <b>Twist Test Method</b>       | IEC 60794-1 E7                        |

## Optical Specifications

|                   |  |
|-------------------|--|
| <b>Fiber Type</b> | G.652.D and G.657.A1, TeraSPEED®   OS2 |
|-------------------|--|

## Optical Specifications, Wavelength Specific

|                             |                   |
|-----------------------------|-------------------|
| <b>Standards Compliance</b> | TIA-492CAAB (OS2) |
|-----------------------------|-------------------|

## Environmental Specifications

|   |   |
|---|---|
| <b>Operating Temperature</b>                        | -20 °C to +70 °C (-4 °F to +158 °F)   |
| <b>Storage Temperature</b>                          | -33 °C to +40 °C (-27.4 °F to +104 °F)  |
| <b>Cable Qualification Standards</b>                | EN 187105   IEC 60794-1-2   |
| <b>EN50575 CPR Cable EuroClass Fire Performance</b> | B2ca  |
| <b>EN50575 CPR Cable EuroClass Smoke Rating</b>     | s1b   |
| <b>EN50575 CPR Cable EuroClass Droplets Rating</b>  | d0  |
| <b>EN50575 CPR Cable EuroClass Acidity Rating</b>   | a1  |
| <b>Environmental Space</b>                          | Aerial, lashed   Buried   Universal Low Smoke Zero Halogen (ULSZH)  |
| <b>Flame Test Method</b>                            | EN 50399   IEC 60331-25 (120) Fire resistance: 120 minutes at 750 °C (no fiber break)   IEC 60332-1-2   IEC 60754-2   IEC 61034-2 |
| <b>Jacket UV Resistance</b>                         | UV stabilized   |
| <b>Water Penetration</b>                            | 24 h  |
| <b>Water Penetration Test Method</b>                | IEC 60794-1 F5  |

## Environmental Test Specifications

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| <b>Low High Bend Test Method</b>     | IEC 60794-1 E11                     |
| <b>Temperature Cycle</b>             | -20 °C to +70 °C (-4 °F to +158 °F) |
| <b>Temperature Cycle Test Method</b> | IEC 60794-1 F1                      |

## Packaging and Weights

### Cable weight

216 kg/km | 145.145 lb/kft

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant



## Included Products

CS-8W-250-EMEA – LightScope ZWP® Singlemode Fiber  
250um

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

## LightScope ZWP® Singlemode Fiber



### Product Classification

|                     |               |
|---------------------|---------------|
| <b>Portfolio</b>    | CommScope®    |
| <b>Product Type</b> | Optical fiber |

### General Specifications

|  |  |
|--|--|
| <b>Cladding Diameter</b>                             | 125 µm                                 |
| <b>Cladding Diameter Tolerance</b>                   | ±0.7 µm                                |
| <b>Cladding Non-Circularity, maximum</b>             | 0.7 %                                  |
| <b>Coating Diameter (Colored)</b>                    | 249 µm                                 |
| <b>Coating Diameter (Uncolored)</b>                  | 242 µm                                 |
| <b>Coating Diameter Tolerance (Colored)</b>          | ±13 µm                                 |
| <b>Coating Diameter Tolerance (Uncolored)</b>        | ±5 µm                                  |
| <b>Coating/Cladding Concentricity Error, maximum</b> | 12 µm                                  |
| <b>Core/Clad Offset, maximum</b>                     | 0.5 µm                                 |
| <b>Proof Test</b>                                    | 689.476 N/mm <sup>2</sup>   100000 psi |

### Dimensions

|                            |                 |
|----------------------------|-----------------|
| <b>Fiber Curl, minimum</b> | 4 m   13.123 ft |
|----------------------------|-----------------|

### Mechanical Specifications

|   |   |
|---|---|
| <b>Macrobending, 20 mm Ø mandrel, 1 turn</b>    | 0.75 dB @ 1,550 nm   1.50 dB @ 1,625 nm |
| <b>Macrobending, 30 mm Ø mandrel, 10 turns</b>  | 0.25 dB @ 1,550 nm   1.00 dB @ 1,625 nm |
| <b>Macrobending, 60 mm Ø mandrel, 100 turns</b> | 0.05 dB @ 1,550 nm   0.05 dB @ 1,625 nm |
| <b>Coating Strip Force, maximum</b>             | 8.9 N   2.001 lbf                       |
| <b>Coating Strip Force, minimum</b>             | 1.3 N   0.292 lbf                       |

# CS-8W-250-EMEA | 250um

**Dynamic Fatigue Parameter, minimum** 20

## Optical Specifications

**Cabled Cutoff Wavelength, maximum** 1250 nm

**Point Defects, maximum** 0.05 dB

**Zero Dispersion Slope, maximum** 0.092 ps/[km-nm-nm]

**Zero Dispersion Wavelength, maximum** 1324 nm

**Zero Dispersion Wavelength, minimum** 1300 nm

## Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.21 dB/km @ 1,550 nm | 0.24 dB/km @ 1625 nm | 0.25 dB/km @ 1,490 nm | 0.35 dB/km @ 1,310 nm | 0.35 dB/km @ 1,385 nm

**Dispersion, maximum** 18 ps(nm-km) at 1550 nm | 2.2 ps(nm-km) at 1625 nm | 3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm

**Index of Refraction** 1.467 @ 1,310 nm | 1.468 @ 1,550 nm

**Mode Field Diameter** 10.4  $\mu\text{m}$  @ 1,550 nm | 9.2  $\mu\text{m}$  @ 1,310 nm

**Mode Field Diameter Tolerance**  $\pm 0.4 \mu\text{m}$  @ 1310 nm |  $\pm 0.5 \mu\text{m}$  @ 1550 nm

**Polarization Mode Dispersion Link Design Value, maximum** 0.06 ps/sqrt(km)

**Standards Compliance** ITU-T G.652.D | ITU-T G.657.A1

## Environmental Specifications

**Heat Aging, maximum** 0.05 dB/km @ 85 °C

**Temperature Dependence, maximum** 0.05 dB/km

**Temperature Humidity Cycling, maximum** 0.05 dB/km

**Water Immersion, maximum** 0.05 dB/km @ 23 °C

## \* Footnotes

**Temperature Dependence, maximum** Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

**Temperature Humidity Cycling, maximum** Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity