

# SSH-114-3

---



SnapStak® Hanger for 1-1/4 in coaxial cable, triple stack capability, includes reinforcement bar

## Product Classification

|                      |                                 |
|----------------------|---------------------------------|
| <b>Product Type</b>  | Hanger kit                      |
| <b>Product Brand</b> | SnapStak®                       |
| <b>Ordering Note</b> | CommScope® non-standard product |

## General Specifications

|                          |                             |
|--------------------------|-----------------------------|
| <b>Cables per Hanger</b> | 1                           |
| <b>Color</b>             | Silver                      |
| <b>Hanger Type</b>       | Snap-in hanger              |
| <b>Mounting</b>          | 3/4 in drilled cable ladder |

## Dimensions

|  |                    |
|--|--------------------|
| <b>Maximum Stack Height</b>            | 3                  |
| <b>Height</b>                          | 40.9 mm   1.61 in  |
| <b>Width</b>                           | 40.1 mm   1.579 in |
| <b>Length</b>                          | 81 mm   3.189 in   |
| <b>Compatible Cable Diameter Range</b> | 37.6–43.2 mm       |
| <b>Compatible Diameter, maximum</b>    | 43.2 mm   1.701 in |
| <b>Compatible Diameter, minimum</b>    | 37.6 mm   1.48 in  |
| <b>Nominal Size</b>                    | 1-1/4 in           |

## Electrical Specifications

|                                    |        |
|------------------------------------|--------|
| <b>Return Loss Effect, maximum</b> | 0.1 dB |
| <b>DTF Effect, maximum</b>         | 0.1 dB |

## Material Specifications

# SSH-114-3

---

**Material Type** Stainless steel

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Corrosion Resistance, minimum with no degradation** ≥500 hours in salt spray chamber

**Environmental Strength Capability** Double cable weight

## Packaging and Weights

**Height, packed** 22 cm | 8.661 in

**Width, packed** 14.6 cm | 5.748 in

**Length, packed** 14.8 cm | 5.827 in

**Packaging quantity** 10

**Weight, gross** 0.52 kg | 1.146 lb

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power