

SSH-158



SnapStak® Hanger for 1-5/8 in coaxial cable

Product Classification

| | |
|----------------------|--------------------------------------|
| Product Type | Hanger kit |
| Product Brand | SnapStak® |
| Ordering Note | CommScope® standard product (Global) |

General Specifications

| | |
|--------------------------|-----------------------------|
| Cables per Hanger | 1 |
| Color | Silver |
| Hanger Type | Snap-in hanger |
| Mounting | 3/4 in drilled cable ladder |

Dimensions

| | |
|--|--------------------|
| Maximum Stack Height | 2 |
| Height | 40.9 mm 1.61 in |
| Width | 50.8 mm 2 in |
| Length | 89.9 mm 3.539 in |
| Compatible Cable Diameter Range | 49–51.1 mm |
| Compatible Diameter, maximum | 51.1 mm 2.012 in |
| Compatible Diameter, minimum | 49 mm 1.929 in |
| Nominal Size | 1-5/8 in |

Electrical Specifications

| | |
|------------------------------------|--------|
| Return Loss Effect, maximum | 0.1 dB |
| DTF Effect, maximum | 0.1 dB |

Material Specifications

SSH-158

Material Type Stainless steel

Mechanical Specifications

Vibration Survival ≥4 hours at resonant frequency

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

Corrosion Resistance, minimum with no degradation ≥500 hours in salt spray chamber

Environmental Strength Capability Double cable weight

Packaging and Weights

Height, packed 22 cm | 8.661 in

Width, packed 15 cm | 5.906 in

Length, packed 14.4 cm | 5.669 in

Packaging quantity 10

Weight, gross 0.6 kg | 1.323 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power