UHVMPMXAL

Base Product



Ultra Low Loss (ULL) Multimode OM5 MPO12 (Unpinned) to MPO12 (Pinned), Armored Pre-terminated Trunk Cable, 96-Fiber, Plenum

Product Classification

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber trunk cable assembly

Product Brand SYSTIMAX ULL

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

General Specifications

Connector A, quantity 8

Color, boot A Black

Color, connector A Lime green

Connector B, quantity 8

Color, boot B Black

Color, connector B Lime green

Construction Type Armored | Stranded

Furcation Color Lime green

Interface, Connector A MPO-12/UPC Female

Interface Feature, connector A Unpinned

Interface, Connector B MPO-12/UPC Male

Interface Feature, connector B Pinned

Jacket Color Lime green

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 12

Total Fibers, quantity 96




UHVMPMXAL

Dimensions

Breakout Length 33 in Cable Assembly Length Range (m) 3 - 999Cable Assembly Length Range (ft) 10 - 999

Ordering Tree



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0° | 4.40 lb @ 90°

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED®

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Indoor | Plenum

Included Products

Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, interlocking aluminum armored with 760230250 P-096-MZ-5G-F12LM

plenum jacket, Multimode OM5, 96 fiber multi-unit with 12 fiber subunits, Lime-green jacket

color, Feet cable marking

MPO12, ULTRA LOW LOSS, FEMALE, OM5, LIME, 3mm 860617232

Page 2 of 10

UHVMPMXAL

860617240

– MPO12, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm



760230250 | P-096-MZ-5G-F12LM



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, interlocking aluminum armored with plenum jacket, Multimode OM5, 96 fiber multiunit with 12 fiber subunits, Lime-green jacket color, Feet cable marking

Product Classification

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

Product Series P-MZ

General Specifications

Armor Type Interlocking aluminum

Cable Type MPO trunk cable

Construction TypeArmoredSubunit TypeGel-free

Jacket Color Lime green

Jacket MarkingFeetSubunit, quantity8Fibers per Subunit, quantity12Total Fiber Count96


Dimensions

Buffer Tube/Subunit Diameter3 mm | 0.118 inDiameter Over Armor18.42 mm | 0.725 inDiameter Over Jacket20.4 mm | 0.803 in

Representative Image



760230250 | P-096-MZ-5G-F12LM



Mechanical Specifications

Minimum Bend Radius, loaded307 mm | 12.087 inMinimum Bend Radius, unloaded204 mm | 8.032 inTensile Load, long term, maximum400 N | 89.924 lbfTensile Load, short term, maximum1335 N | 300.12 lbf

 Compression
 85 N/mm | 485.363 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 35 N-m | 309.776 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 111 m | 364.173 ft

Optical Specifications

Fiber Type OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

Environmental Specifications

Installation temperature 0 °C to +70 °C (+32 °F to +158 °F)

Page 5 of 10



760230250 | P-096-MZ-5G-F12LM

Operating Temperature $0 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (+32 °F to} + 158 \,^{\circ}\text{F)}$

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing NEC OFCP (ETL) and c(ETL)

Flame Test Method NFPA 130 | NFPA 262

Environmental Test Specifications

Heat Age 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

Low High Bend $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle $0 \degree \text{C to } +70 \degree \text{C (} +32 \degree \text{F to } +158 \degree \text{F)}$

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 367 kg/km | 246.613 lb/kft

Regulatory Compliance/Certifications

fication
1

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable





MPO12, ULTRA LOW LOSS, FEMALE, OM5, LIME, 3mm

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorLime greenColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Female

Interface Feature Unpinned

Total Fiber Count 12

Dimensions

 Length
 60.1 mm | 2.366 in

 Compatible Cable Diameter
 3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 ^{\circ}$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED® wideband

Insertion Loss Change, mating 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

COMMSCOPE®

860617232

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.2 dBReturn Loss, minimum27 dB

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

 $\textbf{Insertion Loss Change, temperature} \quad \text{Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)}$





MPO12, ULTRA LOW LOSS, MALE, OM5, LIME, 3mm

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 LazrSPEED®

General Specifications

ColorLime greenColor, bootBlackFerrule GeometryFlat

Interface MPO/UPC Male

Interface FeaturePinnedTotal Fiber Count12

Dimensions

 Length
 60.1 mm | 2.366 in

 Compatible Cable Diameter
 3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum $11.24 \text{ lb} @ 0 ^{\circ}$

Optical Specifications

Fiber Mode Multimode

Fiber Type OM5, LazrSPEED® wideband

Insertion Loss Change, mating 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

COMMSCOPE®

860617240

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.2 dBReturn Loss, minimum27 dB

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted

UK-ROHS Compliant



* Footnotes

Insertion Loss Change, matingTIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

