UG12158-15B4-T



Universal Grounding Kit for HELIAX® 1/2 in through 1-5/8 in corrugated and smoothwall coaxial cable, elliptical waveguide 63 through 180 and Hybrid cables

Product Classification

 Product Type
 Grounding kit

 Product Brand
 HELIAX®

Ordering Note ANDREW® standard product (Global)

General Specifications

Bonding Conductor Jacketing MaterialPVCBonding Conductor MaterialCopperBonding Conductor Wire Size6 gauge

Cable Type Corrugated | Elliptical waveguide | Smoothwall

Color Black

Grounding Kit TypeUniversal Grounding Kits

Grounding Strap MaterialTinned copperLug AttachmentField attachedLug TypeTwo-hole lug

Thread Size 3/8 in

Dimensions

Bonding Conductor Length1524 mm | 60 inCable Jacketing Removal Length, maximum58.42 mm | 2.3 inCable Jacketing Removal Length, minimum55.88 mm | 2.2 inCompatible Diameter, maximum50.8 mm | 2 inCompatible Diameter, minimum15.494 mm | 0.61 in

Nominal Size 1-1/4 in | 1-5/8 in | 1/2 in | 5/8 in | 7/8 in

Waveguide Size WR51-WR137 | WG19-WG14 | R180-R70

ANDREW® an Amphenol company

UG12158-15B4-T

Electrical Specifications

Current Handling Tested to withstand 100,000 amps peak current surge

Current Handling Test Method MIL-STD-1757

Grounding, Bonding and Shielding Test Method MIL-STD-188-124A

Lightning Protection Test MethodIEC 1024-1

Material Specifications

Rivet Material Copper

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+85 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+185 \,^{\circ}\text{F}$)Storage Temperature $-40 \,^{\circ}\text{C}$ to $+80 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+176 \,^{\circ}\text{F}$)

Blowing Rain Test MethodMIL-STD-810, Method 506Corrosion Test MethodMIL-STD-1344, Method 1001Freezing Rain/Icing Test MethodMIL-STD-810, Method 521Humidity Test MethodMIL-STD-1344, Method 1002

Immersion Test MethodIEC 60529:2001, IP68UV Resistance Test MethodMIL-STD-810, Method 505Vibration Test MethodMIL-STD-202, Method 214Weatherproofing MethodButyl and electric tape

Packaging and Weights

 Height, packed
 215.9 mm | 8.5 in

 Width, packed
 152.4 mm | 6 in

 Length, packed
 63.5 mm | 2.5 in

Included Grounding kit | Hardware | Lug | One roll of 2 in PVC tape | One

roll of 24 in butyl rubber tape

Packaging quantity 1

Weight, gross 0.71 kg | 1.565 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value



UG12158-15B4-T

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

42615-10 - Butyl Rubber Tape, 24 in 9905-71 - Black 2 in PVC Tape, 20 ft

* Footnotes

Grounding, Bonding and Shielding Test Method Military Standard for Grounding, Bonding, and Shielding: Bond Resistance

Requirement of a Maximum dc resistance of 0.001 ohm

Lightning Protection Test MethodProtection Against Lightning Electromagnetic Impulse, Table 1—Protection

Level III-IV, 1995-02

