810009825/DB | C-001-DN-8G-M01BK/15G/V6/D



Fiber Drop Cable, Façade, Duct and Aerial, FTTH, 1 fiber, Singlemode, G. 657.A2, Gel-filled, Meters jacket marking, Black jacket, Dca Flame Rating

Product Classification	
Regional Availability	Asia Australia/New Zealand EMEA
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-DN
General Specifications	
Cable Type	Central loose tube Drop Tight buffer
Construction Type	Breakout Non-armored
Subunit Type	Gel-filled
Inner Jacket Color	White
Jacket Color	Black
Jacket Marking	Meters
Jacket Marking Method	Inkjet
Jacket Marking Text	COMMSCOPE GB F.O. CABLE 810009825/DB G657A2 SM 1 FIBER CLASS D [SERIAL NUMBER] [MM/YY] [METRE MARK]
Subunit, quantity	1
Fibers per Subunit, quantity	1
Total Fiber Count	1
Dimensions	
Cable Length	1,999.793 m 6561 ft
Buffer Tube/Subunit Diameter	1.5 mm 0.059 in
Diameter Over Jacket	4.5 mm 0.177 in

Representative Image

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025



810009825/DB | C-001-DN-8G-M01BK/15G/V6/D

Low Smoke Zero-Halogen Jacket Water Blocking E-Glass Ripcord Aramid Yarn 1.5mm Gel Filled Tube **Optical Fiber**



Material Specifications

Jacket Material

Mechanical Specifications

Minimum Bend Radius, loaded 75 mm | 2.953 in Tensile Load, long term, maximum 300 N | 67.443 lbf 1000 N | 224.809 lbf Tensile Load, short term, maximum Compression 10 N/mm | 57.101 lb/in IEC 60794-1 E3 **Compression Test Method** 2 N-m | 17.701 in lb Impact Impact Test Method IEC 60794-1 E4 Strain See long and short term tensile loads Strain Test Method IEC 60794-1 E1 Twist 5 cycles Twist Test Method IEC 60794-1 E7 **Optical Specifications**

Fiber Type

G.657.A2, TeraSPEED®

Low Smoke Zero Halogen (LSZH)

Environmental Specifications

Installation temperature 0 °C to +60 °C (-32 °F to +140 °F) -25 °C to +70 °C (-13 °F to +158 °F) **Operating Temperature**

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025



810009825/DB | C-001-DN-8G-M01BK/15G/V6/D

Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	IEC 60794-1-2
EN50575 CPR Cable EuroClass Fire Perfor	mance Dca
EN50575 CPR Cable EuroClass Smoke Rat	ing s1a
EN50575 CPR Cable EuroClass Droplets Ra	ating d1
EN50575 CPR Cable EuroClass Acidity Rat	ing a1
Environmental Space	Outdoor
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F5
Environmental Test Specifications	
Temperature Cycle	-25 °C to +70 °C (-13 °F to +158 °F)
Temperature Cycle Test Method	IEC 60794-1-22 F1
Packaging and Weights	
Cable weight	26 kg/km 17.471 lb/kft
Included Products	
	Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T 6.657.A2, B2)

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 1, 2025

