

# HFE212-4M4NB



HELIAX® Hybrid Cable Assembly, 2 power conductors 12 AWG Blue /Grey, black jacket, aluminum armor, 4-fiber. End 1: flex angle DLC with boot for RRU. End 2: DLC

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Hybrid cable assembly
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	HFE
<b>Ordering Note</b>	CommScope® non-standard product

## General Specifications


<b>Conductors, quantity</b>	2
<b>Construction Type</b>	Hybrid standard tail
<b>Interface, Connector A</b>	DLC
<b>Interface Feature, connector A</b>	Standard
<b>Interface Body Style, connector A</b>	Flex angle
<b>Interface, Connector B</b>	DLC
<b>Interface Feature, connector B</b>	Standard
<b>Interface Body Style, connector B</b>	Straight
<b>Jacket Color</b>	Black
<b>Total Fibers, quantity</b>	4

## Dimensions


<b>Cable Assembly Length Range (m)</b>	1 – 20
<b>Diameter Over Jacket</b>	13.5 mm   0.531 in
<b>Center Conductor Gauge</b>	12 AWG

## Outline Drawing

# HFE212-4M4NB



## Ordering Tree



## Mechanical Specifications

**Minimum Bend Radius** 134.6 mm | 5.299 in

**Minimum Bend Radius, furcation** 30 mm | 1.181 in

## Optical Specifications

**Fiber Mode** Multimode

# HFE212-4M4NB

---

<b>Fiber Type</b>	OM4, LazrSPEED® 550
<b>Insertion Loss, typical note</b>	Insertion loss is measured at 850 and 1300 nm
<b>Insertion Loss, typical</b>	0.5

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
------------------------------	--------------------------------------

## Packaging and Weights

<b>Cable weight</b>	0.2 kg/m   0.134 lb/ft
---------------------	------------------------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Insertion Loss, typical note** Insertion loss is measured at a room temp of +20°C (+68°F)