

Fiber indoor/outdoor cable, TeraSPEED®, Single Jacket/Single Armor, Low Smoke Zero Halogen (LSZH), Singlemode G.652.D and G.657.A1, 48 fiber, Gel-Free, Stranded Loose Tube, Meters jacket marking, Black jacket color, Cca flame rating

 Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Europe

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series Z-LA

### General Specifications

Armor Type Corrugated steel

Cable Type Stranded loose tube

Construction TypeArmoredSubunit TypeGel-free

Filler, quantity

Jacket ColorBlackJacket MarkingMeters

Subunit, quantity 4

Fibers per Subunit, quantity 12


Total Fiber Count 48

#### **Dimensions**

Buffer Tube/Subunit Diameter2.5 mm | 0.098 inDiameter Over Jacket13 mm | 0.512 in

### Representative Image





### Mechanical Specifications

Minimum Bend Radius, loaded195 mm7.677 inMinimum Bend Radius, unloaded130 mm5.118 inTensile Load, long term, maximum800 N | 179.847 lbf

Tensile Load, short term, maximum 2700 N | 606.984 lbf

 Compression
 22 N/mm | 125.623 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 3 N-m | 26.552 in lb

 Impact Test Method
 FOTP-25 | IEC 60794-1 E4

 Strain Test Method
 FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 461 m | 1,512.467 ft

Optical Specifications

**Fiber Type** G.652.D and G.657.A1, TeraSPEED® | OS2 | OS2

#### **Environmental Specifications**

Installation temperature  $-30 \,^{\circ}\text{C} \, \text{to} + 60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to} + 140 \,^{\circ}\text{F})$ Operating Temperature  $-40 \,^{\circ}\text{C} \, \text{to} + 70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$ Storage Temperature  $-40 \,^{\circ}\text{C} \, \text{to} + 75 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 167 \,^{\circ}\text{F})$ 

Page 2 of 4



Cable Qualification Standards ANSI/ICEA S-104-696 | EN 187105 | Telcordia GR-20 | Telcordia GR-

409

EN50575 CPR Cable EuroClass Fire PerformanceCcaEN50575 CPR Cable EuroClass Smoke Ratings1bEN50575 CPR Cable EuroClass Droplets Ratingd2EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Aerial, lashed | Buried | Low Smoke Zero Halogen (LSZH)

Flame Test Listing EN 50399 | NEC OFC-ST1 (ETL) and c(ETL)

Flame Test Method EN 50399 | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | IEEE

1202 | UL 1685

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

**Environmental Test Specifications** 

Cable Freeze $-2 \, ^{\circ}\text{C}$  $| 28.4 \, ^{\circ}\text{F}$ 

**Cable Freeze Test Method** FOTP-98 | IEC 60794-1 F15

**Heat Age** -40 °C to +85 °C (-40 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

**Low High Bend**  $-30 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-22  $^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

**Temperature Cycle** -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 177 kg/km | 118.939 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CENELEC

Included Products

CS-8W-IOLT - TeraSPEED® OS2 Singlemode Fiber

COMMSCOPE®

\* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable