

# HFT2406-48SV3



HELIAX® Hybrid Cable Assembly, 12X24, Low Inductance, UL Type RHC, 24 power conductors 6 AWG, 48-fiber, 8 alarm wires, PVC jacket, aluminum armor

OBSOLETE

## Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Hybrid cable assembly
Product Brand	HELIAX®
Product Series	HFT
Ordering Note	CommScope® non-standard product

## General Specifications

Alarm Wire, quantity	8
Conductors, quantity	24
Construction Type	Hybrid standard trunk
Interface, Connector A	DLC
Interface Feature, connector A	Standard
Interface Body Style, connector A	Straight
Interface, Connector B	DLC
Interface Feature, connector B	Standard
Interface Body Style, connector B	Straight
Jacket Color	Black
Total Fibers, quantity	48


## Dimensions

Cable Assembly Length Range (ft)	10 – 500
Cord Length	7.62 m   25 ft
Diameter Over Jacket	50.8 mm   2 in

# HFT2406-48SV3

Alarm Wire Gauge	18 AWG
Center Conductor Gauge	6 AWG

## Ordering Tree



## Mechanical Specifications

Minimum Bend Radius	1016 mm   40 in
Minimum Bend Radius, furcation	30 mm   1.181 in

## Optical Specifications

Fiber Type	G.657.A2
Insertion Loss, typical note	Insertion loss is measured at 1310 and 1550 nm
Insertion Loss, typical	0.5

# HFT2406-48SV3

---

## Environmental Specifications

**Operating Temperature** -40 °C to +75 °C (-40 °F to +167 °F)

## Packaging and Weights

**Cable weight** 4.6 kg/m | 3.091 lb/ft

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



### \* Footnotes

**Insertion Loss, typical note** Insertion loss is measured at a room temp of +20°C (+68°F)