0-008-CA-5X-M08BK/28G/093 760252036



Fiber OSP cable, PE, Gel-filled Central Tube, CST, 8 fiber, Multimode OM4, Meters jacket marking, Black jacket color

Product Classification

Regional Availability Asia | Australia/New Zealand

Portfolio CommScope® **Product Type** Fiber OSP cable

Product Series O-LA

General Specifications

Central loose tube **Cable Type**

Armored **Construction Type** Gel-filled **Subunit Type Jacket Color** Black **Jacket Marking** Meters 8

Fibers per Subunit, quantity **Total Fiber Count**

Dimensions

Buffer Tube/Subunit Diameter 2.8 mm | 0.11 in **Diameter Over Jacket** 9.1 mm | 0.358 in

Mechanical Specifications

Minimum Bend Radius, loaded 182 mm | 7.165 in Minimum Bend Radius, unloaded 91 mm | 3.583 in Tensile Load, long term, maximum 890 N | 200.08 lbf 2700 N | 606.984 lbf Tensile Load, short term, maximum

20 N/mm | 114.203 lb/in Compression

IEC 60794-1-2 E3 **Compression Test Method**

Flex 25 cycles

Strain See long and short term tensile loads

COMMSCOPE®

760252036 | 0-008-CA-5X-M08BK/28G/093

Strain Test Method IEC 60794-1-2-E1

Optical Specifications

Fiber Type OM4

Optical Specifications, Wavelength Specific

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Environmental Specifications

Installation temperature -10 °C to +60 °C (+14 °F to +140 °F)

Operating Temperature $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Environmental Space Buried | Ducted | Outdoor

Water Penetration 24 h

Water Penetration Test Method IEC 60794-1 F5B

Environmental Test Specifications

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method IEC 60794-1-2 F1

Packaging and Weights

Cable weight 92 kg/km | 61.821 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-5X-LT-3.0/1.0/093 - OM4 Bend-Insensitive Multimode Fiber

COMMSC**©**PE°

760252036 | 0-008-CA-5X-M08BK/28G/093

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable