

UHA-3C



PIM-Guard®, Universal Three-Way Stand-off Adapter. Mounts snap-in hangers, grommets, and threaded rods onto towers with round members or 1/4" and 3/8" angle members, supporting three stacks for 4-17mm or two stacks for 26-40mm cables

- Attaches onto round and angle tower members with 1/2" banding
- Mounts polymer and metal snap-in hangers
- Mounts rubber grommets
- Includes insert to mount 3/8" threaded rod kits
- Provides three hanger mounting positions
- Optimized to reduce PIM while maximizing structural integrity

Product Classification

Product Type	Adapter
Product Brand	PIM-Guard®
Ordering Note	CommScope® standard product (Global)

General Specifications

Adapter Type	Stand-off adapter
Color	Black
Mounting	3/4 in through hole Tower angle members 1/4 Tower angle members 3/8 Tower round members 1" to 8" diameter

Dimensions

Maximum Stack Height	3
Height	43.688 mm 1.72 in
Outside Width	50.292 mm 1.98 in
Outside Length	76.2 mm 3 in

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Mechanical Specifications

Maximum Loading	Triple stack for hangers SSH-47, SSH-710, SSH-1014, SSH-1416, SSH-411, SSH-1117
Vibration Survival	≥4 hours at resonant frequency

UHA-3C

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
Environmental Strength Capability	Double cable weight
UV Resistance, minimum with no degradation	≥1000 hours

Packaging and Weights

Height, packed	17 cm 6.693 in
Width, packed	13 cm 5.118 in
Length, packed	10 cm 3.937 in
Packaging quantity	10
Weight, gross	0.27 kg 0.595 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power