


# RFFT-36SM-001

---



## HELIAX® Bend Insensitive Singlemode Fiber DLC to DLC 36-Fiber Cable Assembly with pulling grip

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Wireless Fiber Cable Assemblies
<b>Product Series</b>	RFFT
<b>Ordering Note</b>	CommScope® non-standard product

### General Specifications


<b>Construction Type</b>	Discrete fiber trunk
<b>Interface, Connector A</b>	DLC
<b>Interface Feature, connector A</b>	Uniboot
<b>Interface Body Style, connector A</b>	Straight
<b>Interface, Connector B</b>	DLC
<b>Interface Feature, connector B</b>	Uniboot
<b>Interface Body Style, connector B</b>	Straight
<b>Jacket Color</b>	Black
<b>Total Fibers, quantity</b>	36

### Dimensions

<b>Cable Assembly Length Range (m)</b>	15 – 570
<b>Diameter Over Jacket</b>	10.28 mm   0.405 in

### Ordering Tree

# RFFT-36SM-001



## Mechanical Specifications

<b>Minimum Bend Radius</b>	103 mm   4.055 in
<b>Minimum Bend Radius, furcation</b>	30 mm   1.181 in

## Optical Specifications

<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, typical note</b>	Insertion loss is measured at 1310 and 1550 nm
<b>Insertion Loss, typical</b>	0.5

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Environmental Space</b>	Indoor   Outdoor

## Packaging and Weights

<b>Cable weight</b>	91 kg/km   61.149 lb/kft
---------------------	--------------------------

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>

# RFFT-36SM-001

---

ROHS Compliant

UK-ROHS Compliant



## \* Footnotes

**Insertion Loss, typical note** Insertion loss is measured at a room temp of +20°C (+68°F)