



Fiber indoor/outdoor cable, Loose Tube Gel-filled, 24 fiber, Singlemode G.652.D and G.657.A1, Meters jacket marking, Black jacket color

Product Classification

Regional Availability	Asia Australia/New Zealand
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-LN


General Specifications

Cable Type	Stranded loose tube
Construction Type	Non-armored
Fiber Type, quantity	24
Fibers per Subunit, quantity	6
Jacket Color	Black
Jacket Marking	Meters
Subunit Type	Gel-filled
Total Fiber Count	24

Dimensions

Buffer Tube/Subunit Diameter	1.8 mm 0.071 in
Diameter Over Jacket	10 mm 0.394 in

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded	200 mm 7.874 in
Minimum Bend Radius, unloaded	100 mm 3.937 in
Tensile Load, long term, maximum	890 N 200.08 lbf
Tensile Load, short term, maximum	2700 N 606.984 lbf
Compression	10 N/mm 57.101 lb/in
Compression Test Method	IEC 60794-1-2 E3
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1-21 E1

Optical Specifications

Fiber Type	G.652.D and G.657.A1 OS2
-------------------	----------------------------

Optical Specifications, Wavelength Specific

Attenuation, maximum	0.30 dB/km @ 1,550 nm 0.40 dB/km @ 1,310 nm
-----------------------------	---

Environmental Specifications

Installation temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Buried Ducted Indoor/Outdoor Low Smoke Zero Halogen (LSZH)
Flame Test Method	IEC 60332-1
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F5C

Environmental Test Specifications

Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	IEC 60794-1-2 F1

Packaging and Weights

Cable weight	107 kg/km 71.901 lb/kft
---------------------	---------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



Included Products

CS-8Z-LT	- Low Water Peak, Dispersion-Unshifted Singlemode Fiber
----------	---

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable