
9-1592145-1 | C-012-DS-5K-MSUOR/GY/C



Indoor/outdoor Fiber Optic Cable, 12-fiber, office distribution, multimode, OM4, ULSZH, orange. Provides Rodent Resistance.

- · designed to offer flexibility, strength and compact construction for internal and interbuilding use
- non-metallic construction reinforced by E-glass yarns, which provide rodent resistance and higher tensile strength
- oversheathed with a ULSZH jacket meeting IEC fire performance requirements

Product Classification

Regional AvailabilityAsia | EMEAPortfolioCommScope®

Product Type Fiber indoor/outdoor cable

Product Series C-DS

General Specifications

Cable TypeTight buffer

Jacket ColorOrangeJacket MarkingMetersJacket Marking MethodInkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE 9-1592145-1 12x50/125 OM4 EN50575

CLASS C ULSZH [Serial NUMBER] [METRE MARK]

Strength Members E-glass yarns

Fibers per Subunit, quantity 12

Total Fiber Count 12

Dimensions

Diameter Over Jacket 8 mm | 0.315 in

Mechanical Specifications

Minimum Bend Radius, loaded150 mm | 5.906 inMinimum Bend Radius, unloaded90 mm | 3.543 inTensile Load, short term, maximum1500 N | 337.214 lbf

Cable Crush Resistance, maximum 20 N/mm | 114.203 lb/in

Optical Specifications

COMMSC PE°

9-1592145-1 | C-012-DS-5K-MSUOR/GY/C

Fiber Type OM4, LazrSPEED®

Optical Specifications, Wavelength Specific

Standards Compliance IEC 60794-1 | TIA-492AAAD (OM4)

Environmental Specifications

Installation temperature $-5 \,^{\circ}\text{C}$ to $+50 \,^{\circ}\text{C}$ (+23 $^{\circ}\text{F}$ to +122 $^{\circ}\text{F}$)

Operating Temperature $-20 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-20 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

EN50575 CPR Cable EuroClass Fire PerformanceCcaEN50575 CPR Cable EuroClass Smoke Ratings2EN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Universal Low Smoke Zero Halogen (ULSZH)

Packaging and Weights

Cable weight 69 kg/km | 46.366 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-5K-LT – LazrSPEED® 550 OM4 Bend-Insensitive Multimode

Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

COMMSCOPE®

LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

LazrSPEED® 550

Product Classification

Portfolio CommScope®

Product Type Optical fiber

General Specifications

Cladding Diameter 125 µm

Cladding Diameter Tolerance $\pm 5 \, \mu m$

Cladding Non-Circularity, maximum 1 %

Coating Diameter (Colored) 254 µm

Coating Diameter (Uncolored) 245 µm

Coating Diameter Tolerance (Colored) ±7 μm

Coating Diameter Tolerance (Uncolored) ±10 µm

Coating/Cladding Concentricity Error, maximum 12 µm

Core Diameter 50 µm

Core Diameter Tolerance ±2.5 μm

Core/Clad Offset, maximum 1.5 μm

Proof Tensile Stress 100,000 psi (0.69 GPa)

Mechanical Specifications

Macrobending, 15 mm Ø mandrel, 2 turns 0.20 dB @ 850 nm | 0.50 dB @ 1,300 nm

Macrobending, 30 mm Ø mandrel, 2 turns 0.10 dB @ 850 nm | 0.30 dB @ 1,300 nm

Macrobending, 75 mm Ø mandrel, 100 turns 0.50 dB @ 1,300 nm | 0.50 dB @ 850 nm

Coating Strip Force, maximum 8.9 N | 2.001 lbf

Coating Strip Force, minimum 1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 18

Optical Specifications

Numerical Aperture 0.2

COMMSCOPE®

CS-5K-LT

Numerical Aperture Tolerance±0.015Point Defects, maximum0.15 dB

Zero Dispersion Slope, maximum 0.105 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum 1316 nm **Zero Dispersion Wavelength, minimum** 1297 nm

Optical Specifications, Wavelength Specific

1 Gbps Ethernet Distance 1,110 m @ 850 nm | 600 m @ 1,300 nm

10 Gbps Ethernet Distance 550 m @ 850 nm

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Backscatter Coefficient -68.0 dB @ 850 nm | -75.7 dB @ 1,300 nm

 Bandwidth, Laser, minimum
 4,700 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

 Bandwidth, OFL, minimum
 3,500 MHz-km @ 850 nm | 500 MHz-km @ 1,300 nm

Differential Mode Delay 0.70 ps/m @ 850 nm

Differential Mode Delay Note Superior to ANSI/TIA TIA-492AAAF and IEC 60793-2-10 at 850 nm

Index of Refraction 1.479 @ 1,300 nm | 1.483 @ 850 nm

Standards Compliance ANSI/TIA-492AAAF (OM4) | IEC 60793-2-10, A1 (OM4)

Environmental Specifications

Heat Aging, maximum 0.20 dB/km @ 85 °C

Temperature Dependence, maximum0.1 dB/kmTemperature Humidity Cycling, maximum0.2 dB/km

Water Immersion, maximum 0.20 dB/km @ 23 °C

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Temperature Dependence, maximum Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

COMMSCOPE®