

8-port sector antenna, 4x 617-894 and 4x 1695-2200 MHz, 65° HPBW, 2x RET

 Antenna includes 2xSingle Column X-Pol Arrays for 617-894MHz and 2xSingle Column X-Pol Arrays for 1695-2200MHz

#### General Specifications

Antenna Type Sector

Band Multiband

Color Light Gray (RAL 7035)

**Grounding Type**RF connector inner conductor and body grounded to reflector and mounting

bracket

Performance Note Outdoor usage

Radome Material Fiberglass, UV resistant

**Reflector Material** Aluminum **RF Connector Interface** 4.3-10 Female

RF Connector Location

RF Connector Quantity, high band

RF Connector Quantity, mid band

4

RF Connector Quantity, low band

4

Remote Electrical Tilt (RET) Information

**RET Hardware** CommRET v2

RET Interface 8-pin DIN Female | 8-pin DIN Male

**RET Interface, quantity** 1 female | 1 male

Input Voltage 10-30 Vdc

Internal RET Low band (1) | Mid band (1)

Power Consumption, active state, maximum 10 W Power Consumption, idle state, maximum 2 W

Dimensions

RF Connector Quantity, total

**Width** 498 mm | 19.606 in


ANDREW® an Amphenol company

**Depth** 197 mm | 7.756 in

**Length** 1828 mm | 71.969 in

Net Weight, antenna only 28.6 kg | 63.052 lb

#### Array Layout



Array ID	Frequency (MHz)	RF Connector	RET (SRET)	AISG No.	AISG RET UID	
R1	617-894	1 - 2	4	AICC1	CD	
R2	617-894	3 - 4	-	AISG1	CPxxxxxxxxxxxxxxR1	
B1	1695-2200	5 - 6	1	AICC1	CD::::::::::::::::::::::::::::::::::::	
B2	1695-2200	7 - 8	2	2	AISG1	CPxxxxxxxxxxxxxxB1

(Sizes of colored boxes are not true depictions of array sizes)

### Port Configuration



### **Electrical Specifications**

**Impedance** 50 ohm

**Operating Frequency Band** 1695 – 2200 MHz | 617 – 894 MHz

Polarization ±45°

**Total Input Power, maximum** 900 W @ 50 °C

### **Electrical Specifications**

ANDREW® an Amphenol company

	R1,R2	R1,R2	B1,B2	B1,B2
Frequency Band, MHz	617-728	814-894	1695-1780	1995-2200
RF Port	1,2,3,4	1,2,3,4	5,6,7,8	5,6,7,8
Gain, dBi	14.6	15.3	18.1	18.8
Beamwidth, Horizontal, degrees	64	63	68	67
Beamwidth, Vertical, degrees	14.3	12.3	5.7	4.8
Beam Tilt, degrees	2-14	2-14	2-12	2-12
USLS (First Lobe), dB	15	16	17	18
Front-to-Back Ratio at 180°, dB	28	27	30	30
Isolation, Cross Polarization, dB	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25
VSWR   Return loss, dB	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	250	250	200	200

### Mechanical Specifications

Effective Projective Area (EPA), frontal	0.58 m <sup>2</sup>   6.243 ft <sup>2</sup>
Effective Projective Area (EPA), lateral	0.18 m²   1.938 ft²
Wind Loading @ Velocity, frontal	622.0 N @ 150 km/h (139.8 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	188.0 N @ 150 km/h (42.3 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	746.0 N @ 150 km/h (167.7 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	428.0 N @ 150 km/h (96.2 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

### Packaging and Weights

Width, packed	565 mm   22.244 in
Depth, packed	309 mm   12.165 in
Length, packed	2015 mm   79.331 in
Weight, gross	40.3 kg   88.846 lb

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

BSAMNT-2F – Mounting bracket for cylindrical pipe installations (60-115mm pipe diameter) for fix mechanical tilt applications.

### \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance

