

760253133 | 30" Pole Cab 90" Tall Base With Round Shaft



Bottom of the Pole, 30in Square by 90" tall 4G/5G capable Multi Carrier Concealment Enclosure to house and conceal multiple low to high power radios and any other wireless infrastructure equipment in a cabinet at the base of the pole.

- Intended to house and conceal multiple radios and any other wireless infrastructure equipment in a cabinet at the base of the pole
- Flexible configuration accepts low to high-power single or dual band radios, Integrated AC load center/OVP and Disconnect and integrated AC/DC rectifier options

Available with Pole Top concealment, mmWave 5G mounting, luminaire arms.

Available After Market Kits -- ordered separately:

- 860665491-AMK-001 - Ericsson 4480/4415/8863 Radios & 6304 PSU Mounting Kit

- 860665491-AMK-002 - Ericsson 4478/4490/4890 Radio Mounting Kit

- 860665491-AMK-004 - Ericsson 8843/4449/4478/4890/4490& 630x PSU Mounting Kit

Product Classification

Product Type	Pole cab
Product Brand	Metro Cell
Ordering Note	ANDREW® standard product with terms
Warranty	One year

General Specifications

Antenna Compatibility, ANDREW	ANDREW Canister Antennas Panel Antenna
Antenna Compatibility, Other Vendors	ACE AMPHENOL GALTRONICS GAMMA NU JMA KATHREIN KMW ROSENBERG
Color	Light Gray (RAL 7035)
Color Options	Black (RAL 9005) Brown (RAL 8014) Metallic Silver
Compatible Foundation Type	Poured Concrete Pre-Cast Concrete
Compatible Smart Devices	Cameras Digital Signage Emergency Call Station Environmental Monitoring Security Lighting
Cooling	Air conditioned Fan Cooling
Power Supply Compatibility	DELTA 2.0 PSU-AC-08
Radio Compatibility, ANDREW	CAP H
Radio Compatibility, Ericsson	1281 220x 440x 4415 4426 4449 4478 6701 8843 8863 Diplexer
Radio Compatibility, Nokia	AEUB AEWB AEWD /AEWE AHBCA AHFIA AHFIB AHFIC AHIA AHIB AHLBA AHLBBA AZRB

760253133 | 30" Pole Cab 90" Tall Base With Round Shaft

Radio Compatibility Samsung AT1K01 | AT1K02 | AT1K0X | Diplexer | RF4402D-D1A | RFV01U-D1A | RFV01U-D2A | RT246A | RT4401-48A

Radios Included None

Dimensions

Height 2,286 mm | 90 in

Pole Height Options 10.668 m | 35 ft | 12.192 m | 40 ft | 6.096 m | 20 ft | 7.62 m | 25 ft | 9.144 m | 30 ft

Width 762 mm | 30 in

Depth 762 mm | 30 in

Depth Note Square

Pole Diameter 203.2 mm | 8 in

Electrical Specifications

Input Voltage 230–115 Vac

Generator Connection No connection

Material Specifications

Finish Aluminum Chromate

Finish Concealment Covers Powder coated

Material Type Steel

Environmental Specifications

Thermal Compliance GR-487