
810009926/DB | D-012-LN-8W-M12NS-CY04



Fiber OSP cable, LightScope® ZWP Single Jacket All-Dielectric, 12 fiber, Gel-Free, Stranded Loose Tube, Singlemode G.652.D and G.657.Al, Meters jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

 Portfolio
 CommScope®

 Product Type
 Fiber OSP cable

Product Series D-LN

General Specifications

Cable Type Stranded loose tube

Construction Type Non-armored

Subunit Type Gel-free

Filler, quantity 4

Jacket Color Black
Jacket Marking Meters

Subunit, quantity 1

Fibers per Subunit, quantity 12

Total Fiber Count 12


Dimensions

Buffer Tube/Subunit Diameter2.5 mm | 0.098 inDiameter Over Jacket10.2 mm | 0.402 in

Representative Image



810009926/DB | D-012-LN-8W-M12NS-CY04



Material Specifications

Jacket Material PE

Mechanical Specifications

Minimum Bend Radius, loaded153 mm | 6.024 inMinimum Bend Radius, unloaded102 mm | 4.016 inTensile Load, long term, maximum800 N | 179.847 lbfTensile Load, short term, maximum2700 N | 606.984 lbf

 Compression
 22 N/mm | 125.623 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

Impact 4.41 N-m | 39.032 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 1307 m | 4,288.058 ft

Optical Specifications

Fiber Type G.652.D and G.657.A1 | G.652.D and G.657.A1



810009926/DB | D-012-LN-8W-M12NS-CY04

Environmental Specifications

Installation temperature $-30 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-22 °F to +158 °F)

Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 °F to +158 °F)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+75 \,^{\circ}\text{C}$ (-40 °F to +167 °F)

Cable Qualification Standards ANSI/ICEA S-87-640 | EN 187105 | Telcordia GR-20

Environmental Space Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

Heat Age $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Heat Age Test Method IEC 60794-1 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method FOTP-37 | IEC 60794-1 E11

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 63 kg/km | 42.334 lb/kft

Included Products

DB-8W-LT - LightScope® ZWP Singlemode

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable



LightScope® ZWP Singlemode Fiber



Product Classification

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

Cladding Diameter 125 µm **Cladding Diameter Tolerance** ±0.7 µm Cladding Non-Circularity, maximum 0.7 % **Coating Diameter (Colored)** 249 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 μm **Coating Diameter Tolerance (Uncolored)** ±5 µm Coating/Cladding Concentricity Error, maximum 12 µm **Core Diameter** 8.3 µm Core/Clad Offset, maximum $0.5 \, \mu m$

Proof Tensile Stress 100,000 psi (0.69 GPa)

Dimensions

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.75 dB @ 1,550 nm
 | 1.50 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.25 dB @ 1,550 nm
 | 1.00 dB @ 1,625 nm

 Macrobending, 60 mm Ø mandrel, 100 turns
 0.05 dB @ 1,550 nm
 | 0.05 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

COMMSCOPE®

DB-8W-LT

Optical Specifications

Cabled Cutoff Wavelength, maximum1260 nmPoint Defects, maximum0.1 dB

Zero Dispersion Slope, maximum 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1300 nm

Optical Specifications, Wavelength Specific

Attenuation, maximum 0.22 dB/km @ 1,550 nm | 0.25 dB/km @ 1,490

nm | 0.25 dB/km @ 1,625 nm | 0.36 dB/km @ 1,310

nm | 0.36 dB/km @ 1,385 nm

Attenuation, typical 0.19 dB/km @ 1,550 nm | 0.33 dB/km @ 1,310 nm

Backscatter Coefficient -79.6 dB @ 1,310 nm | -82.1 dB @ 1,550 nm

Dispersion, maximum 18 ps(nm-km) at 1550 nm | 3.5 ps(nm-km) from 1285

nm to 1330 nm at 1310 nm

Index of Refraction 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

Mode Field Diameter $10.4 \, \mu \text{m} \ @ \ 1,550 \, \text{nm} \ | \ 9.2 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ @ \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ | \ 1,310 \, \text{nm} \ | \ 9.6 \, \mu \text{m} \ | \ 1,310 \, \text{nm} \ | \ 1,310$

1,385 nm

@ 1385 nm

Polarization Mode Dispersion Link Design Value, maximum 0.04 ps/sgrt(km)

Standards Compliance ITU-T G.652.D | ITU-T G.657.A1

Environmental Specifications

Heat Aging, maximum 0.05 dB/km @ 85 °C

 Temperature Dependence, maximum
 0.05 dB/km

 Temperature Humidity Cycling, maximum
 0.05 dB/km

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

COMMSCOPE®

DB-8W-LT

Temperature Dependence, maximum

Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

Temperature Humidity Cycling, maximum Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity

COMMSCOPE®