760251947 | C-008-CN-5Y-M08BK/28G/093



Fiber indoor/outdoor cable, Gel-filled Central Tube, 8 fiber, Multimode OM3, Meters jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand

Portfolio CommScope®

Product Type Fiber indoor/outdoor cable

Product Series Z-CN

General Specifications

Cable Type Central loose tube

Construction Type Non-armored

Subunit Type Gel-filled

Jacket Color Black

Jacket Marking Meters

Fibers per Subunit, quantity 8

Total Fiber Count 8

Dimensions


Buffer Tube/Subunit Diameter 2.8 mm | 0.11 in

Diameter Over Jacket 7 mm | 0.276 in

Representative Image



760251947 | C-008-CN-5Y-M08BK/28G/093



Mechanical Specifications

Minimum Bend Radius, loaded 140 mm | 5.512 in

Minimum Bend Radius, unloaded 70 mm | 2.756 in

Tensile Load, long term, maximum 800 N | 179.847 lbf

Tensile Load, short term, maximum 1800 N | 404.656 lbf

Compression 15 N/mm | 85.652 lb/in

Compression Test Method IEC 60794-1-2 E3

Strain See long and short term tensile loads

Strain Test Method IEC 60794-1-2-E1

Optical Specifications

Fiber Type OM3

Optical Specifications, Wavelength Specific

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Environmental Specifications

Installation temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)Operating Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to +158 $^{\circ}\text{F}$)Environmental SpaceLow Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60332-1

COMMSCOPE®

760251947 | C-008-CN-5Y-M08BK/28G/093

Environmental Test Specifications

Temperature Cycle $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method IEC 60794-1-2 F1

Packaging and Weights

Cable weight 58 kg/km | 38.974 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

