

Fiber OSP cable, Triple Jacket, Anti Termite, All-Dielectric, 6 fiber, Gel Filled, Mini Stranded Loose Tube, Singlemode G.652.D, Meters jacket marking, Black jacket color

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber OSP cable
<b>Product Series</b>	O-N3


## General Specifications

<b>Cable Type</b>	Stranded loose tube
<b>Subunit Type</b>	Gel-filled
<b>Filler, quantity</b>	5
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters   Meters
<b>Subunit, quantity</b>	1
<b>Fibers per Subunit, quantity</b>	6
<b>Total Fiber Count</b>	6

## Dimensions

<b>Buffer Tube/Subunit Diameter</b>	1.55 mm   0.061 in
<b>Diameter Over Jacket</b>	7.3 mm   0.287 in

## Representative Image



## Material Specifications

**Jacket Material** Alternative jacket PE | Nylon | PE

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	150 mm   5.906 in
<b>Minimum Bend Radius, unloaded</b>	75 mm   2.953 in
<b>Tensile Load, long and short term</b>	See Sag and Tension tables in Product Documentation section
<b>Tensile Load, long term, maximum</b>	1000 N   224.809 lbf
<b>Compression</b>	20 N/mm   114.203 lb/in
<b>Compression Test Method</b>	IEC 60794-1-21 E3
<b>Flex</b>	25 cycles
<b>Impact</b>	1 N-m   8.851 in lb
<b>Impact Test Method</b>	IEC 60794-1-21 E4
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	IEC 60794-1-21 E1
<b>Twist</b>	10 cycles
<b>Twist Test Method</b>	IEC 60794-1-21 E7

## Optical Specifications

**Fiber Type** G.652.D

## Optical Specifications, Wavelength Specific

# 760252623 | O-006-N3-8M-M06BK/PE/PA/PE

---

**Attenuation, maximum** 0.21 dB/km @ 1,550 nm | 0.35 dB/km @ 1,310 nm

## Environmental Specifications

**Installation temperature** 0 °C to +50 °C (+32 °F to +122 °F)  
**Operating Temperature** -10 °C to +70 °C (+14 °F to +158 °F)  
**Storage Temperature** -20 °C to +70 °C (-4 °F to +158 °F)  
**Cable Qualification Standards** IEC 60794-5-10  
**Jacket UV Resistance** UV stabilized  
**Water Penetration** 24 h  
**Water Penetration Test Method** IEC 60794-1 F5

## Environmental Test Specifications

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)  
**Heat Age Test Method** IEC 60794-1 F9  
**Low High Bend Test Method** IEC 60794-1 E11  
**Temperature Cycle Test Method** IEC 60794-1 F1

## Packaging and Weights

**Cable weight** 43 kg/km | 28.895 lb/kft

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable