760252022 | 0-002-CN-5Y-M02BK/28G/093



Fiber OSP cable, PE, Gel-filled Central Tube, All-dielectric, 2-fiber, Multimode OM3, Meters jacket marking, Black jacket color

Product Classification

Regional Availability

Asia | Australia/New Zealand

Portfolio CommScope®
Product Type Fiber OSP cable

Product Series O-CN

General Specifications

Cable Type Central loose tube

Construction Type Non-armored

Subunit Type Gel-filled

Jacket Color Black

Jacket Marking Meters

Fibers per Subunit, quantity 2

Total Fiber Count 2


Dimensions

Buffer Tube/Subunit Diameter 2.8 mm | 0.11 in Diameter Over Jacket 6 mm | 0.236 in

Representative Image



760252022 | 0-002-CN-5Y-M02BK/28G/093



Material Specifications

Jacket Material PE

Mechanical Specifications

Minimum Bend Radius, loaded120 mm | 4.724 inMinimum Bend Radius, unloaded60 mm | 2.362 inTensile Load, long term, maximum300 N | 67.443 lbfTensile Load, short term, maximum1000 N | 224.809 lbfCompression15 N/mm | 85.652 lb/in

Compression Test Method IEC 60794-1-2 E3

Flex 25 cycles

Strain See long and short term tensile loads

Strain Test Method IEC 60794-1-2-E1

Optical Specifications

Fiber Type OM3

Optical Specifications, Wavelength Specific

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Environmental Specifications

Installation temperature -10 °C to +60 °C (+14 °F to +140 °F)

COMMSCOPE®

760252022 | 0-002-CN-5Y-M02BK/28G/093

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ ($-40 \,^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Environmental Space Buried | Ducted | Outdoor

Water Penetration 24 h

Water Penetration Test Method IEC 60794-1 F5C

Environmental Test Specifications

Temperature Cycle -40 °C to +70 °C (-40 °F to +158 °F)

Temperature Cycle Test Method IEC 60794-1-2 F1

Packaging and Weights

Cable weight 35 kg/km | 23.519 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

