884064004/10 | CS41CM BLU C6A 4/23 U/UTP RL 305M



CS41CM, ETL Verified Category 6A U/UTP Cable, non-plenum, blue jacket, 4 pair count, 1000 ft (305 m) length reel

Product Classification

Regional Availability Asia | Australia/New Zealand **NETCONNECT®** Portfolio **Product Type** Twisted pair cable General Specifications **Product Number** CS41CM 6A **ANSI/TIA Category** Cable Component Type Horizontal U/UTP (unshielded) Cable Type Conductor Type, singles Solid 8 Conductors, quantity Blue **Jacket Color** Pairs, quantity 4 Separator Type Isolator Transmission Standards ANSI/TIA-568.2-D | IEC 61156-5 Dimensions 204.9 m + 1000 ftCable Langth

Cable Length	304.8111 100011
Diameter Over Insulated Conductor	1.113 mm 0.044 in
Diameter Over Jacket, nominal	7.087 mm 0.279 in
Jacket Thickness	0.508 mm 0.02 in
Conductor Gauge, singles	23 AWG

Cross Section Drawing

Page 1 of 4



884064004/10 | CS41CM BLU C6A 4/23 U/UTP RL 305M

Jacket ———	
Insulation ———	
Isolator	
Conductor ———	
Таре	

Electrical Specifications

dc Resistance Unbalance, maximum	4 %
dc Resistance, maximum	8 ohms/100 m 2.438 ohms/100 ft
Delay Skew, maximum	45 ns
Dielectric Strength, minimum	1500 Vac 2500 Vdc
Mutual Capacitance at Frequency	5.6 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	67 %
Operating Frequency, maximum	500 MHz
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A
Safety Voltage Rating	300 V

Page 2 of 4



Electrical Cable Performance

CS STD	CommScope Refers to the standard value listed under Transmission Standards in th	e Electrical Specificat	ions above
ТҮР	Typical Electrical Performance		
IL	Insertion Loss (dB/100m)	NEXT	Near End Crosstalk (dB/100m)
ACR	Attenuation to Crosstalk Ratio (dB/100m)	PSNEXT	Power Sum Near End Crosstalk (db/100m)
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)	ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)
PSACRF	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)	RL	Return Loss (dB)
TCL	Transverse Conversion Loss (dB/100m)	ELTCTL	Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL.	NEXT STD	ACR	PSNEXT	PSACR	ACRF	PSACRF STD	RL
	STD		STD	STD	STD	STD		STD
1	2.1	75.3	73.2	72.3	70.2	68	65	20
4	3.8	66.3	62.5	63.3	59.5	55.9	53	23
8	5.3	61.7	56.4	58.7	53.4	49.9	46.9	24.5
10	5.9	60.3	54.4	57.3	51.4	48	45	25
16	7.5	57.2	49.7	54.2	46.7	43.9	40.9	25
20	8.4	55.8	47.4	52.8	44.4	42	39	25
25	9.4	54.3	44.9	51.3	41.9	40	37	24.3
31.25	10.5	52.9	42.4	49.9	39.4	38.1	35.1	23.6
62.5	15	48.4	33.4	45.4	30.4	32.1	29.1	21.5
100	19.1	45.3	26.2	42.3	23.2	28	25	20.1
155	24.1	42.4	18.3	39.4	15.3	24.2	21.2	18.8
200	27.6	40.8	13.2	37.8	10.2	22	19	18
250	31.1	39.3	8.3	36.3	5.3	20	17	17.3
300	34.3	38.1	3.9	35.1	0.9	18.4	15.5	16.8
350	37.2	37.1	-0.1	34.1	-3.1	17.1	14.1	16.3
400	40.1	36.3	-3.8	33.3	-6.8	15.9	13	15.9
500	45.3	34.8	-10.5	31.8	-13.5	14	11	15.2

Material Specifications

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	PVC
Separator Material	Polyolefin
Tape Material	Poly/Aluminum/Poly
Mechanical Specifications	

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications

Page 3 of 4



884064004/10 | CS41CM BLU C6A 4/23 U/UTP RL 305M

Installation temperature	0 °C to +60 °C (+32 °F to +140 °F)		
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)		
Environmental Space	Non-plenum		
Flame Test Method	CM NEC Article 800 UL 1685 UL 910		
Packaging and Weights			
Cable weight	46.297 kg/km 31.11 lb/kft		
Packaging Type	Reel		
Regulatory Compliance/Certifications			

Agency Classification CHINA-ROHS Below maximum concentration value

 REACH-SVHC
 Compliant as per SVHC revision on www.commscope.com/ProductCompliance

 ROHS
 Compliant

 UK-ROHS
 Compliant



Page 4 of 4

