## 760242092 | OCM8-SP112LLG-40DB



OCM8 Fiber Optic Splitter Module, Planar, 1x2 Splitter, singlemode, LC /APC, symmetrical split ratio, 4 m pigtails

## **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | EMEA | India | Latin

America | North America

Product Type Splitter module

Product Series OCM8

General Specifications

**Functionality** Splitting

**Technology Type** Planar lightwave circuit (PLC)

**Distribution Type** 1 x 2 splitter

 Interface, Input
 LC/APC

 Interface, Output
 LC/APC

Split Ratio Symmetrical

Splitter, quantity 1

Dimensions

 Height
 5 mm | 0.197 in

 Depth
 45 mm | 1.772 in

 Length
 100 mm | 3.937 in

Pigtail Length, Input 4 m | 13.123 ft

Pigtail Length, Output 4 m | 13.123 ft

Pigtail Diameter, Input1.8 mm | 0.071 in

Pigtail Diameter, Output 1.8 mm | 0.071 in

**Optical Specifications** 

Fiber Type G.657.A1

Directivity, minimum 55 dB

Polarization Dependent Loss, maximum 0.2 dB

**COMMSCOPE®** 

## 760242092 | OCM8-SP112LLG-40DB

Uniformity, maximum 0.85 dB

Wavelength Range 1260–1650 nm

Insertion Loss, Splitter, maximum4.2 dBReturn Loss, Connector, minimum55 dB

**Environmental Specifications** 

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$ 

Packaging and Weights

Packaging quantity

