## 760242986 | OCM8-SP124LLG-20DB



OCM8 Fiber Optic Splitter Module, Planar, 2x4 Splitter, singlemode, LC /APC, symmetrical split ratio, 2 m pigtails

#### Product Classification

Regional Availability	Asia   Australia/New Zealand   China   EMEA   India   Latin America   North America
Product Type	Splitter module
Product Series	OCM8
General Specifications	
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Distribution Type	2 x 4 splitter
Interface, Input	LC/APC
Interface, Output	LC/APC
Split Ratio	Symmetrical
Splitter, quantity	1
Dimensions	
Height	5 mm   0.197 in
Depth	45 mm   1.772 in
Length	100 mm   3.937 in
Pigtail Length, Input	2 m   6.562 ft
Pigtail Length, Output	2 m   6.562 ft
Pigtail Diameter, Input	1.8 mm   0.071 in
Pigtail Diameter, Output	1.8 mm   0.071 in
Optical Specifications	
Fiber Type	G.657.A1
Directivity, minimum	55 dB
Polarization Dependent Loss, maximum	0.3 dB

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 8, 2024



# 760242986 | OCM8-SP124LLG-20DB

Uniformity, maximum	1.65 dB
Wavelength Range	1260-1650 nm
Insertion Loss, Splitter, maximum	8 dB
Return Loss, Connector, minimum	55 dB

#### **Environmental Specifications**

**Operating Temperature** 

-40 °C to +70 °C (-40 °F to +158 °F)

### Packaging and Weights

Packaging quantity

1

#### Regulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSBelow maximum concentration valueREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductComplianceROHSCompliantUK-ROHSCompliant





©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 8, 2024

