


1RU-SP2164001 | 1RU SPLTR PNL 1X64 UPC/LC



1RU panel, 1X64 split ratio, 1 splitter, LC/UPC connectors

- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	Asia Australia/New Zealand China EMEA India Latin America North America
Product Type	Splitter patch panel
Product Series	1RU
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Distribution Type	1 x 64 splitter
Interface, Input	LC/UPC
Interface, Output	LC/UPC
Splitter, quantity	1

Dimensions

Height	43.69 mm 1.72 in
Width	482.6 mm 19 in
Length	199.89 mm 7.87 in

Optical Specifications

Directivity, minimum	55 dB
Polarization Dependent Loss, maximum	0.4 dB
Uniformity, maximum	2.3 dB
Wavelength Range	1260–1650 nm
Insertion Loss, Splitter, maximum	21 dB

1RU-SP2164001 | 1RU SPLTR PNL 1X64 UPC/LC

Return Loss, Splitter, minimum 50 dB

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity 5%–95%, non-condensing

Packaging and Weights

Packaging quantity 1