# 760253279 | 0-024-N3-8M-M12BL/PE/PA/PE



Fiber OSP cable, Triple Jacket, Anti Termite, All-Dielectric, 24 fiber, Gel Filled, Mini Stranded Loose Tube, Singlemode G.652.D, Feet jacket marking, Black jacket color

#### **Product Classification**

Regional Availability Asia | Australia/New Zealand

Portfolio CommScope®
Product Type Fiber OSP cable

**Product Series** O-N3

General Specifications

Cable Type Stranded loose tube

Subunit Type Gel-filled

Filler, quantity

Jacket Color Black

Jacket Marking Meters

Subunit, quantity 2
Fibers per Subunit, quantity 12
Total Fiber Count 24


Dimensions

Buffer Tube/Subunit Diameter1.55 mm0.061 inDiameter Over Jacket7.3 mm0.287 in

Representative Image



# 760253279 | 0-024-N3-8M-M12BL/PE/PA/PE



### Material Specifications

Jacket Material Alternative jacket PE | Nylon | PE

Mechanical Specifications

Minimum Bend Radius, loaded150 mm5.906 inMinimum Bend Radius, unloaded75 mm2.953 in

**Tensile Load, long and short term**See Sag and Tension tables in Product Documentation section

**Tensile Load, long term, maximum** 1000 N | 224.809 lbf

**Compression** 20 N/mm | 114.203 lb/in

**Compression Test Method** IEC 60794-1 E3

Flex 25 cycles

**Impact** 1 N-m | 8.851 in lb

Impact Test Method IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method IEC 60794-1 E1

Twist 10 cycles

Twist Test Method IEC 60794-1-21 E7

**Optical Specifications** 

**Fiber Type** G.652.D

Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.21 dB/km @ 1,550 nm | 0.35 dB/km @ 1,310 nm

**COMMSCOPE®** 

# 760253279 | 0-024-N3-8M-M12BL/PE/PA/PE

### **Environmental Specifications**

**Installation temperature** 0 °C to +50 °C (+32 °F to +122 °F)

**Operating Temperature**  $-10 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C (+14 °F to +158 °F)}$ 

**Storage Temperature**  $-20 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-4 °F to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards IEC 60794-5-10

Jacket UV Resistance UV stabilized

Water Penetration 24 h

**Water Penetration Test Method** IEC 60794-1 F5

### **Environmental Test Specifications**

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test MethodIEC 60794-1 F9Low High Bend Test MethodIEC 60794-1 E11

Packaging and Weights

**Temperature Cycle Test Method** 

**Cable weight** 43 kg/km | 28.895 lb/kft

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

IEC 60794-1 F1

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

