

FFV4Q4-65D-R7



20-port sector antenna, 4x 617-894, 8x 1695-2690 MHz 65° HPBW and 8x 2500-4000 MHz, Beamformer, 7x RET

- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Cluster connectors for the beam-forming array, including eight RF ports plus one calibration port

General Specifications

Antenna Type	Sector and beamforming
Band	Multiband
Calibration Connector Interface	M-LOC
Calibration Connector Quantity	1
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female M-LOC
RF Connector Location	Bottom
RF Connector Quantity, high band	8
RF Connector Quantity, mid band	8
RF Connector Quantity, low band	4
RF Connector Quantity, total	20

Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male
Input Voltage	10–30 Vdc
Internal RET	High band (1) Low band (2) Mid band (4)
Power Consumption, active state, maximum	8 W
Power Consumption, idle state, maximum	1 W

FFV4Q4-65D-R7

Protocol 3GPP/AISG 2.0 (Single RET)

Dimensions


Width 498 mm | 19.606 in

Depth 197 mm | 7.756 in

Length 2688 mm | 105.827 in

TDD Column Spacing 58 mm | 2.283 in

Array Layout



Array ID	Frequency (MHz)	RF Connector	RET (SRET)	AISG No.	AISG RET UID
R1	617-894	1 - 2	1	AISG1	CPxxxxxxxxxxxxxxxxR1
R2	617-894	3 - 4	2	AISG1	CPxxxxxxxxxxxxxxxxR2
Y1	1695-2690	5 - 6	3	AISG1	CPxxxxxxxxxxxxxxxxY1
Y2	1695-2690	7 - 8	4	AISG1	CPxxxxxxxxxxxxxxxxY2
Y3	1695-2690	9 - 10	5	AISG1	CPxxxxxxxxxxxxxxxxY3
Y4	1695-2690	11 - 12	6	AISG1	CPxxxxxxxxxxxxxxxxY4
P1	2500-4000	13 - 20	7	AISG1	CPxxxxxxxxxxxxxxxxP1


(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration

FFV4Q4-65D-R7



Logo Image



Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2690 MHz 2500 – 4000 MHz 617 – 894 MHz
Polarization	±45°
Total Input Power, maximum	1,400 W @ 50 °C

FFV4Q4-65D-R7

Electrical Specifications

	R1,R2	R1,R2	Y1-Y4	Y1-Y4	Y1-Y4	P1	P1	P1
Frequency Band, MHz	617–698	698–894	1695–1920	1920–2200	2490–2690	2500–2690	3300–3800	3700–4000
RF Port	1,2,3,4	1,2,3,4	5-12	5-12	5-12	13-20	13-20	13-20
Gain, dBi	15.2	16.1	16.6	17.3	17.6	16	16.4	15.9
Beamwidth, Horizontal, degrees	69	60	60	57	49	90	66	64
Beamwidth, Vertical, degrees	9.5	8.1	6.5	5.9	5.2	5.9	6	6.2
Beam Tilt, degrees	2–12	2–12	2–12	2–12	2–12	2–12	2–12	2–12
USLS (First Lobe), dB	16	17	15	16	15	17	15	15
Front-to-Back Ratio at 180°, dB	29	29	35	34	30	33	27	25
Coupling level, Amp, Antenna port to Cal port, dB						26	26	26
Coupling level, max Amp Δ, Antenna port to Cal port, dB						±2	±2	±2
Coupler, max Amp Δ, Antenna port to Cal port, dB						0.9	0.9	0.9
Coupler, max Phase Δ, Antenna port to Cal port, degrees						7	7	7
Isolation, Cross Polarization, dB	25	25	25	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25	25	25
Isolation, Co-polarization, dB						18	18	18
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-140	-140	-140
Input Power per Port at 50°C, maximum, watts	250	250	200	200	200	80	80	80

Electrical Specifications, Broadcast 65°

	2500–2690	3300–3800	3700–4000
Frequency Band, MHz			
Gain, dBi	18.2	17.4	16.6
Beamwidth, Horizontal, degrees	55	59	61
Beamwidth, Vertical, degrees	5.9	5.9	6.2
Front-to-Back Total Power at 180° ± 30°, dB	30	23	19
USLS (First Lobe), dB	17	17	17

FFV4Q4-65D-R7

Electrical Specifications, Envelope Pattern

Frequency Band, MHz	2500–2690	3300–3800	3700–4000
Gain, dBi	21	21	20.6
Beamwidth, Horizontal at 10 dB, degrees	120	125	126
Beamwidth, Vertical at 3 dB, degrees	5.8	6	6
Front-to-Back Total Power at 180° ± 30°, dB	31	26	23
USLS (First Lobe), dB	19	18	16

Electrical Specifications, Service Beam

Frequency Band, MHz	2500–2690	3300–3800	3700–4000
Steered 0° Gain, dBi	20.4	20.9	20.4
Steered 0° Beamwidth, Horizontal, degrees	25	19	19
Steered 0° Front-to-Back Total Power at 180° ± 30°, dB	33	28	25
Steered 0° Horizontal Sidelobe, dB	13	11	11
Steered 30° Gain, dBi	20.3	19.3	18.8
Steered 30° Beamwidth, Horizontal, degrees	27	22	18
Steered 30° Front-to-Back Total Power at 180° ± 30°, dB	32	26	23

Electrical Specifications, Soft Split

Frequency Band, MHz	2500–2690
Gain, dBi	20.2
Beamwidth, Horizontal, degrees	30
Front-to-Back Total Power at 180° ± 30°, dB	32
Horizontal Sidelobe, dB	17

Mechanical Specifications

Wind Loading @ Velocity, frontal	970.0 N @ 150 km/h (218.1 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	304.0 N @ 150 km/h (68.3 lbf @ 150 km/h)

FFV4Q4-65D-R7

Wind Loading @ Velocity, maximum	1,162.0 N @ 150 km/h (261.2 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	667.0 N @ 150 km/h (149.9 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	565 mm 22.244 in
Depth, packed	309 mm 12.165 in
Length, packed	2935 mm 115.551 in
Weight, gross	70.5 kg 155.426 lb
Weight, net	47.2 kg 104.058 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

- | | | |
|-----------|---|--|
| BSAMNT-4 | - | Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set. |
| BSAMNT-M4 | - | Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set. |

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
-------------------------	---

BSAMNT-4



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

Application Outdoor

Color Silver

Dimensions

Compatible Diameter, maximum 115 mm | 4.528 in

Compatible Diameter, minimum 60 mm | 2.362 in

Weight, net 6.5 kg | 14.33 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



BSAMNT-M4



Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

Application Outdoor

Color Silver

Dimensions

Compatible Diameter, maximum 115 mm | 4.528 in

Compatible Diameter, minimum 60 mm | 2.362 in

Weight, net 4.6 kg | 10.141 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

