

# 20-port sector antenna, 4x 617-894, 8x 1695-2690 MHz 65° HPBW and 8x 2500-4000 MHz, Beamformer, 7x RET

- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Cluster connectors for the beam-forming array, including eight RF ports plus one calibration port

### General Specifications

Antenna Type Sector and beamforming

BandMultibandCalibration Connector InterfaceM-LOCCalibration Connector Quantity1

Color Light Gray (RAL 7035)

**Grounding Type**RF connector inner conductor and body grounded to reflector and mounting

bracket

Performance Note Outdoor usage

**Radome Material** Fiberglass, UV resistant

**Reflector Material** Aluminum

**RF Connector Interface** 4.3-10 Female | M-LOC

RF Connector Location Bottom

RF Connector Quantity, high band 8
RF Connector Quantity, mid band 8
RF Connector Quantity, low band 4
RF Connector Quantity, total 20

### Remote Electrical Tilt (RET) Information

**RET Hardware** CommRET v2

**RET Interface** 8-pin DIN Female | 8-pin DIN Male

**RET Interface, quantity** 1 female | 1 male

Input Voltage 10-30 Vdc

Internal RET High band (1) | Low band (2) | Mid band (4)

Power Consumption, active state, maximum 8 W
Power Consumption, idle state, maximum 1 W



**Protocol** 3GPP/AISG 2.0 (Single RET)

**Dimensions** 


**Width** 498 mm | 19.606 in

**Depth** 197 mm | 7.756 in

**Length** 2688 mm | 105.827 in

**TDD Column Spacing** 58 mm | 2.283 in

### Array Layout




Array ID	Frequency (MHz)	RF Connector	RET (SRET)	AISG No.	AISG RET UID
R1	617-894	1 - 2	1	AISG1	CPxxxxxxxxxxxxxR1
R2	617-894	3 - 4	2	AISG1	CPxxxxxxxxxxxxxR2
Y1	1695-2690	5 - 6	3	AISG1	CPxxxxxxxxxxxxxY1
Y2	1695-2690	7 - 8	4	AISG1	CPxxxxxxxxxxxxxY2
Y3	1695-2690	9 - 10	5	AISG1	CPxxxxxxxxxxxxxY3
Y4	1695-2690	11 - 12	6	AISG1	CPxxxxxxxxxxxxx4
P1	2500-4000	13 - 20	7	AISG1	CPxxxxxxxxxxxxxxP1

(Sizes of colored boxes are not true depictions of array sizes)

### Port Configuration



### Logo Image



### **Electrical Specifications**

**Impedance** 50 ohm

**Operating Frequency Band** 1695 – 2690 MHz | 2500 – 4000 MHz | 617 – 894 MHz

Polarization ±45°

**Total Input Power, maximum** 1,400 W @ 50 °C

ANDREW® an Amphenol company

## **Electrical Specifications**

	R1,R2	R1,R2	Y1-Y4	Y1-Y4	Y1-Y4	P1	P1	P1
Frequency Band, MHz	617-698	698-894	1695-192	0 1920-220	0 2490-269	0 2500-269	0 3300–380	0 3700-4000
RF Port	1,2,3,4	1,2,3,4	5-12	5-12	5-12	13-20	13-20	13-20
Gain, dBi	15.2	16.1	16.6	17.3	17.6	16	16.4	15.9
Beamwidth, Horizontal, degrees	69	60	60	57	49	90	66	64
Beamwidth, Vertical, degrees	9.5	8.1	6.5	5.9	5.2	5.9	6	6.2
Beam Tilt, degrees	2-12	2-12	2-12	2-12	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	16	17	15	16	15	17	15	15
Front-to-Back Ratio at 180°, dB	29	29	35	34	30	33	27	25
Coupling level, Amp, Antenna port to Cal port, dB						26	26	26
Coupling level, max Amp $\Delta$ , Antenna port to Cal port, dB						±2	±2	±2
Coupler, max Amp $\Delta$ , Antenna port to Cal port, dB						0.9	0.9	0.9
Coupler, max Phase Δ, Antenna port to Cal port, degrees						7	7	7
Isolation, Cross Polarization, dB	25	25	25	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25	25	25
Isolation, Co-polarization, dB						18	18	18
VSWR   Return loss, dB	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-140	-140	-140
Input Power per Port at 50°C, maximum, watts	250	250	200	200	200	80	80	80

## Electrical Specifications, Broadcast 65°

Frequency Band, MHz	2500-2690	3300-3800	3700-4000
Gain, dBi	18.2	17.4	16.6
Beamwidth, Horizontal, degrees	55	59	61
Beamwidth, Vertical, degrees	5.9	5.9	6.2
Front-to-Back Total Power at 180° ± 30°, dB	30	23	19
USLS (First Lobe), dB	17	17	17

Page 4 of 6



Frequency Band, MHz	2500-2690 3300-3800 3700-4000		
Gain, dBi	21	21	20.6
Beamwidth, Horizontal at 10 dB, degrees	120	125	126
Beamwidth, Vertical at 3 dB, degrees	5.8	6	6
Front-to-Back Total Power at 180° ± 30°, dB	31	26	23
USLS (First Lobe), dB	19	18	16

### Electrical Specifications, Service Beam

Frequency Band, MHz	2500-269	0 3300–380	0 3700-4000
Steered 0° Gain, dBi	20.4	20.9	20.4
Steered 0° Beamwidth, Horizontal, degrees	25	19	19
Steered 0° Front-to-Back Total Power at 180° ± 30°, dB	33	28	25
Steered 0° Horizontal Sidelobe, dB	13	11	11
Steered 30° Gain, dBi	20.3	19.3	18.8
Steered 30° Beamwidth, Horizontal, degrees	27	22	18
Steered 30° Front-to-Back Total Power at 180° ± 30°, dB	32	26	23

## Electrical Specifications, Soft Split

Frequency Band, MHz	2500-2690
Gain, dBi	20.2
Beamwidth, Horizontal, degrees	30
Front-to-Back Total Power at 180° ± 30°, dB	32
Horizontal Sidelobe, dB	17

## Mechanical Specifications

 Wind Loading @ Velocity, frontal
 970.0 N @ 150 km/h (218.1 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 304.0 N @ 150 km/h (68.3 lbf @ 150 km/h)

ANDREW® an Amphenol company

**Wind Loading @ Velocity, maximum** 1,162.0 N @ 150 km/h (261.2 lbf @ 150 km/h)

 $\textbf{Wind Loading @ Velocity, rear} \hspace{1.5cm} 667.0 \text{ N } \textcircled{a} \hspace{0.1cm} 150 \hspace{0.1cm} \text{km/h} \hspace{0.1cm} (149.9 \hspace{0.1cm} \text{lbf} \hspace{0.1cm} \textcircled{a} \hspace{0.1cm} 150 \hspace{0.1cm} \text{km/h})$ 

Wind Speed, maximum 241 km/h (150 mph)

### Packaging and Weights

 Width, packed
 565 mm | 22.244 in

 Depth, packed
 309 mm | 12.165 in

 Length, packed
 2935 mm | 115.551 in

 Weight, gross
 70.5 kg | 155.426 lb

 Weight, net
 47.2 kg | 104.058 lb

### Regulatory Compliance/Certifications

#### Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

#### Included Products

BSAMNT-4 – Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members.

Kit contains one scissor top bracket set and one bottom bracket set.

BSAMNT-M4 – Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round

members. Kit contains one scissor bracket set.

### \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance

