



Fiber indoor cable, Low Smoke Zero Halogen Indoor Distribution, 8 fiber single-unit, Multimode OM5, Meters jacket marking, Lime green jacket color

Product Classification

Regional Availability	China
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	L-DS
Country Specific for	China

General Specifications

Cable Type	Tight buffer
Jacket Color	Lime green
Jacket Marking	Meters
Strength Members	E-glass yarns
Total Fiber Count	8

Dimensions

Buffer Tube/Subunit Diameter	0.9 mm 0.035 in
Diameter Over Jacket	6 mm 0.236 in

Mechanical Specifications

Minimum Bend Radius, loaded	120 mm 4.724 in
Minimum Bend Radius, unloaded	60 mm 2.362 in
Tensile Load, long and short term	See Sag and Tension tables in Product Documentation section
Tensile Load, long term, maximum	198 N 44.512 lbf
Tensile Load, short term, maximum	660 N 148.374 lbf
Compression	10 N/mm 57.101 lb/in
Compression Test Method	IEC 60794-1-2 E3
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1-2-E1

Optical Specifications

Fiber Type OM5

Optical Specifications, Wavelength Specific

Attenuation, maximum 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Environmental Specifications

Installation temperature -10 °C to +60 °C (+14 °F to +140 °F)

Operating Temperature -20 °C to +70 °C (-4 °F to +158 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Cable Qualification Standards Telcordia GR-409

Environmental Space Low Smoke Zero Halogen (LSZH)

Flame Test Listing B1

Flame Test Method GB/T 31247

Environmental Test Specifications

Temperature Cycle -20 °C to +70 °C (-4 °F to +158 °F)

Temperature Cycle Test Method IEC 60794-1-2 F1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

CS-5C-TB-3.0/1.0/093 – OM5 WideBand Multimode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable