760242983 | OCM8-SP12GLLG-20DB



OCM8 Fiber Optic Splitter Module, Planar, 2x16 Splitter, singlemode, LC /APC, symmetrical split ratio, 2 m pigtails

Product Classification

Regional Availability	Asia Australia/New Zealand China EMEA India Latin America North America
Product Type	Splitter module
Product Series	OCM8
General Specifications	
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Distribution Type	2 x 16 splitter
Interface, Input	LC/APC
Interface, Output	LC/APC
Split Ratio	Symmetrical
Splitter, quantity	1
Dimensions	
Height	10 mm 0.394 in
Depth	45 mm 1.772 in
Length	100 mm 3.937 in
Pigtail Length, Input	2 m 6.562 ft
Pigtail Length, Output	2 m 6.562 ft
Pigtail Diameter, Input	1.8 mm 0.071 in
Pigtail Diameter, Output	1.8 mm 0.071 in
Optical Specifications	
Fiber Type	G.657.A1
Directivity, minimum	55 dB
Polarization Dependent Loss, maximum	0.4 dB

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 8, 2024



760242983 | OCM8-SP12GLLG-20DB

Uniformity, maximum	2.25 dB
Wavelength Range	1260-1650 nm
Insertion Loss, Splitter, maximum	14.8 dB
Return Loss, Connector, minimum	55 dB

Environmental Specifications

Operating Temperature-40 °C to +70 °C (-40 °F to +158 °F)Packaging and Weights1

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 8, 2024

