


SFG22HD-10-3-96



G22HD High Capacity Sector Frame with 2 7/8in OD x 10.5ft face.
Includes three 2 3/8in OD x 96in antenna pipes.

Product Classification

Regional Availability	North America
Product Type	High capacity Tower sector frame
Product Series	G2
Ordering Note	ANDREW® standard product in the United States and Canada
Warranty	One year

General Specifications

Application	4G LTE antenna/radio mount
Mounting	Angle 60°, 203.2 mm (8 in) Straight or tapered legs up to 203.2 mm (8 in) OD
Patent Number	Patent pending
Pipe, quantity	3
Sectors, quantity	1
Tower Taper	Non-tapered Tapered

Dimensions

Height	2,438.4 mm 96 in
Face Width	3.2 m 10.5 ft
Width	3,200.4 mm 126 in
Pipe Length	2,438.4 mm 96 in
Face Support Pipe Diameter	73.025 mm 2.875 in
Mounting Diameter, maximum	218.44 mm 8.6 in
Mounting Diameter, minimum	38.1 mm 1.5 in
Pipe Outer Diameter	60.325 mm 2.375 in
Stand-off Distance	1,041.4 mm 41 in

Material Specifications

Material Type	Hot dip galvanized steel
---------------	--------------------------

SFG22HD-10-3-96

Mechanical Specifications

Wind Rating	For Specifications, please contact your local ANDREW representative
Wind Rating Test Method	TIA/EIA-222-G

Packaging and Weights

Included	Frame Pipe mounts Plain end pipes (3) Stiff arms (2) Tower attachment
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code