884065204/10 | CS44ZB1 BLU C6A 4/23 F/UTP RL 305M



CS44ZB1 Category 6A, F/UTP Cable, low smoke zero halogen, blue jacket, 4 pair count, 1000 ft (305 m) length reel

Product Classification

Regional Availability China

Portfolio NETCONNECT®

Product Type Twisted pair cable

General Specifications

Product Number CS44ZB

ANSI/TIA Category 6A

Cable Component Type Horizontal

Cable Type F/UTP (shielded)

Conductor Type, singlesSolidConductors, quantity8Drain Wire TypeSolidJacket ColorBluePairs, quantity4

Separator Type Isolator

Transmission Standards ANSI/TIA-568.2-D | ISO/IEC 11801 Class EA | YD/T 1019

Dimensions


Cable Length304.8 m | 1000 ftDiameter Over Insulated Conductor1.14 mm | 0.045 inDiameter Over Jacket, nominal7.391 mm | 0.291 in

Conductor Gauge, singles23 AWGDrain Wire Gauge26 AWG

Cross Section Drawing



884065204/10 | CS44ZB1 BLU C6A 4/23 F/UTP **RL 305M**



Electrical Specifications

Characteristic Impedance Tolerance

Characteristic Impedance 100 ohm ±15 ohm

dc Resistance, maximum 6.66 ohms/100 m | 2.03 ohms/100 ft

Delay Skew, maximum 45 ns

Dielectric Strength, minimum 1500 Vac | 2500 Vdc

Mutual Capacitance at Frequency 5.6 nF/100 m @ 500 MHz

Nominal Velocity of Propagation (NVP) 64 %

Operating Voltage, maximum 80 V

Remote Powering Fully complies with the recommendations set forth by IEEE 802.3 bt (Type 4) for the safe delivery of power over LAN cable when

installed according to ISO/IEC 14763-2, CENELEC EN 50174-1,

CENELEC EN 50174-2 or TIA TSB-184-A

Segregation Class

Material Specifications

Conductor Material Bare copper Insulation Material Polyolefin

Jacket Material Low Smoke Zero Halogen (LSZH)

Shield (Tape) Material Aluminum/Polyester

Mechanical Specifications

Pulling Tension, maximum 10.206 kg | 22.5 lb



884065204/10 | CS44ZB1 BLU C6A 4/23 F/UTP RL 305M

Environmental Specifications

Installation temperature 0 °C to +60 °C (+32 °F to +140 °F)

Operating Temperature $-20 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ ($-4 \,^{\circ}\text{F}$ to $+140 \,^{\circ}\text{F}$)

Acid Gas Test Method IEC 60754-2

EN50575 CPR Cable EuroClass Fire Performance No Rating

GB 31247 Cable China Class Fire Performance B1

GB 31247 Cable China Class Smoke Toxicity Rating t0

GB 31247 Cable China Class Droplets Rating d0

GB 31247 Cable China Class Acidity/Corrosion Rating a1

Environmental Space Low Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60332-1

Smoke Test Method IEC 61034-2

Packaging and Weights

Packaging Type Reel

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

