## UGVRZRZ8L

#### **Base Product**



Ultra Low Loss (ULL) OM5 MPO16 APC (Pinned) to MPO16 APC (Pinned), Fiber Trunk Cable Assembly, 96-Fiber, Plenum

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

### General Specifications

Connector A, quantity 6

Color, boot A Black

Color, connector A Green

Connector B, quantity 6

Color, boot B Black

Color, connector B Green

Construction Type Stranded

**Furcation Color** Lime green

Interface, Connector A MPO-16/APC Male

Interface, Connector B MPO-16/APC Male

**Jacket Color** Lime green

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 16

Total Fibers, quantity 96

Dimensions

Breakout Length 22 in


Page 1 of 8

## UGVRZRZ8L

Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 10 - 999

### Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

**Optical Specifications** 

**Fiber Mode** Multimode

**Fiber Type** OM5, LazrSPEED®

### **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$ 

Environmental Space Indoor | Plenum

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## UGVRZRZ8L

#### Included Products

760251010 P-096-MP-5G-F16LM

860659158

- Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 96 fiber multi-unit with 16 fiber subunits,
   Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color
- Fiber Optic Connector Kit, multimode, OM3/OM4, MPO-16/APC, ULL, pinned, green, for 3 mm cable



## 760251010 | P-096-MP-5G-F16LM



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 96 fiber multi-unit with 16 fiber subunits, Multimode OM5, Gel-free, Feet jacket marking, Lime green jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

**Product Series** P-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

**Subunit Type** Gel-free

Jacket Color Lime green

Jacket Marking Feet

Subunit, quantity 6

Fibers per Subunit, quantity 16

Total Fiber Count 96

**Dimensions** 

**Buffer Tube/Subunit Diameter** 3 mm | 0.118 in

**Diameter Over Jacket** 10.7 mm | 0.421 in

Mechanical Specifications

Minimum Bend Radius, loaded 161 mm | 6.339 in

Minimum Bend Radius, unloaded 107 mm | 4.213 in

Tensile Load, long term, maximum 400 N | 89.924 lbf

Tensile Load, short term, maximum 1335 N | 300.12 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3



## 760251010 | P-096-MP-5G-F16LM

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

Strain See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 368 m | 1,207.349 ft

**Optical Specifications** 

Fiber Type OM5, LazrSPEED® wideband | OM5, LazrSPEED® wideband

### **Environmental Specifications**

Installation temperature  $0 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ Operating Temperature  $0 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ Storage Temperature  $-40 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ 

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

### **Environmental Test Specifications**

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

 Low High Bend
 0 °C to +70 °C (+32 °F to +158 °F)

 Low High Bend Test Method
 FOTP-37 | IEC 60794-1 E11

 Temperature Cycle
 0 °C to +70 °C (+32 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 113 kg/km | 75.932 lb/kft

\* Footnotes

**COMMSCOPE®** 

# 760251010 | P-096-MP-5G-F16LM

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

## 860659158



Fiber Optic Connector Kit, multimode, OM3/OM4, MPO-16/APC, ULL, pinned, green, for 3 mm cable

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connectorProduct BrandLazrSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Male

Interface FeaturePinnedTotal Fiber Count16

**Dimensions** 

Length60.1 mm | 2.366 inCompatible Cable Diameter3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 ^{\circ}$ 

Optical Specifications

Fiber ModeMultimodeFiber TypeOM3 | OM4

**Insertion Loss Change, mating** 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

**COMMSCOPE®** 

## 860659158

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.2 dB

### Packaging and Weights

Packaging quantity 1

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

**Insertion Loss Change, mating**TIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

