# UJGQXUCTH

#### **Base Product**



Ultra Low Loss (ULL) Singlemode MPO8 (Pinned) to unconnectorized, Fiber Trunk Cable Assembly, 48-Fiber, Dual Rated (OFNR/LSZH)

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

### General Specifications

Connector A, quantity 6

Color, boot AGrayColor, connector AGreenConnector B, quantity0

Construction Type Stranded
Furcation Color Yellow

Interface, Connector A MPO-08/APC Male

Interface, Connector B Unterminated

Jacket Color Yellow

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 48

**Dimensions** 


Breakout Length22 inCable Assembly Length Range (m)3 - 305Cable Assembly Length Range (ft)10 - 999

Page 1 of 8



# UJGQXUCTH

### Ordering Tree



#### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$  | 4.40 lb @ 90  $^{\circ}$ 

**Optical Specifications** 

Fiber Mode Singlemode

**Fiber Type** G.657.A2, TeraSPEED®

### **Environmental Specifications**

Operating Temperature  $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 °F to +140 °F)}$ 

Environmental Space Dual Rated LSZH/Riser | Indoor

#### Regulatory Compliance/Certifications

Agency Classification
ANATEL Compliant

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



#### Included Products

760245573 N-048-MP-8G1-F08YL/20T/D Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 48 fiber multi-unit with 8 fiber 2.0 mm subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Dca flame

Page 2 of 8



# UJGQXUCTH

rating

860659022

– MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm

### 760245573 | N-048-MP-8G1-F08YL/20T/D



Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk, 48 fiber multi-unit with 8 fiber 2.0 mm subunits, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Dca flame rating

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

PortfolioCommScope®Product TypeFiber indoor cable

**Product Series** N-MP

General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

Subunit TypeGel-freeJacket ColorYellowJacket MarkingFeetSubunit, quantity6

Fibers per Subunit, quantity 8

Total Fiber Count 48

**Dimensions** 

**Buffer Tube/Subunit Diameter** 2 mm | 0.079 in

**Diameter Over Jacket** 8.2 mm | 0.323 in

Mechanical Specifications

**Compression Test Method** 

Minimum Bend Radius, loaded 123 mm | 4.843 in

Minimum Bend Radius, unloaded 82 mm | 3.228 in

**Tensile Load, long term, maximum** 200 N | 44.962 lbf

**Tensile Load, short term, maximum** 667 N | 149.948 lbf

**Compression** 10 N/mm | 57.101 lb/in

Page 4 of 8



FOTP-41 | IEC 60794-1 E3

## 760245573 | N-048-MP-8G1-F08YL/20T/D

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

Vertical Rise, maximum 295 m | 967.848 ft

**Optical Specifications** 

**Fiber Type** G.657.A2/B2 | G.657.A2/B2

### **Environmental Specifications**

Installation temperature  $0 \, ^{\circ}\text{C} \, \text{to} +60 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} +140 \, ^{\circ}\text{F})$ Operating Temperature  $0 \, ^{\circ}\text{C} \, \text{to} +70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} +158 \, ^{\circ}\text{F})$ Storage Temperature  $-40 \, ^{\circ}\text{C} \, \text{to} +70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F} \, \text{to} +158 \, ^{\circ}\text{F})$ 

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

EN50575 CPR Cable EuroClass Fire PerformanceDcaEN50575 CPR Cable EuroClass Smoke Ratings1aEN50575 CPR Cable EuroClass Droplets Ratingd1EN50575 CPR Cable EuroClass Acidity Ratinga1

Environmental Space Low Smoke Zero Halogen (LSZH) | Riser

Flame Test Listing NEC OFNR-ST1 (ETL) and c(ETL)

Flame Test Method | IEC 60332-3 | IEC 60754-2 | IEC 61034-2 | UL 1666 | UL 1685

### **Environmental Test Specifications**

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

 Low High Bend
 -20 °C to +70 °C (-4 °F to +158 °F)

 Low High Bend Test Method
 FOTP-37 | IEC 60794-1 E11

 Temperature Cycle
 0 °C to +70 °C (+32 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

**COMMSCOPE®** 

## 760245573 | N-048-MP-8G1-F08YL/20T/D

### Packaging and Weights

**Cable weight** 55 kg/km | 36.958 lb/kft

#### Regulatory Compliance/Certifications

Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant UK-ROHS Compliant



### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



## 860659022



#### MPO-08, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 2mm

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Fiber connector

 Product Brand
 TeraSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Male

Interface Feature Pinned

Total Fiber Count 8

**Dimensions** 

**Compatible Cable Diameter** 2 mm | 0.079 in

Material Specifications

Ferrule Material Polymer

Optical Specifications

**Fiber Mode** Singlemode Fiber Type G.657.A2

Optical Components Standard ANSI/TIA-568-C.3

Insertion Loss, maximum0.35 dBReturn Loss, minimum65 dB

Packaging and Weights

**COMMSCOPE®** 

## 860659022

#### **Packaging quantity**

1

### Regulatory Compliance/Certifications

Agency	Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

