## UJXRZRZ8M

#### **Base Product**



Ultra Low Loss (ULL) OM4 MPO16 APC (Pinned) to MPO16 APC (Pinned), Fiber Trunk Cable Assembly, 144-Fiber, Dual Rated (OFNR/LSZH)

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | China | Europe | India | Latin

America | Middle East/Africa | North America

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales Representative | For

lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may

vary based on cable configuration

## General Specifications

Connector A, quantity 9

Color, boot A Black

Color, connector A Green

Connector B, quantity 9

Color, boot B Black

Construction Type Stranded

Furcation Color Agua

Interface, Connector A MPO-16/APC Male

Interface, Connector B MPO-16/APC Male

Jacket Color Agua

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 16

Total Fibers, quantity 144

Dimensions

Color, connector B

Breakout Length 22 in

Page 1 of 8


Green

## **UJXRZRZ8M**

Cable Assembly Length Range (m) 3 - 305

Cable Assembly Length Range (ft) 10 - 999

## Ordering Tree



## Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$  | 4.40 lb @ 90  $^{\circ}$ 

**Optical Specifications** 

Fiber Mode Multimode

**Fiber Type** OM4, LazrSPEED®

## **Environmental Specifications**

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Environmental Space Dual Rated LSZH/Riser | Indoor

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



# UJXRZRZ8M

### Included Products

760251061 N-144-MP-5K-F16AQ/30T/B2 Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk Cable, 144 fiber with 16-fiber, 3.0mm subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color, B2ca flame rating

860659158

Fiber Optic Connector Kit, multimode, OM3/OM4, MPO-16/APC, ULL, pinned, green, for 3 mm cable



# 760251061 | N-144-MP-5K-F16AQ/30T/B2



Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk Cable, 144 fiber with 16-fiber, 3.0mm subunits, Gel-free, Multimode OM4, Feet jacket marking, Aqua jacket color, B2ca flame rating

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** N-MP

General Specifications

 Cable Type
 MPO trunk cable

Construction Type Non-armored

**Subunit Type** Gel-free

**Jacket Color** Aqua

Jacket Marking Feet

Subunit, quantity 9

Fibers per Subunit, quantity 16

Total Fiber Count 144

Dimensions

**Buffer Tube/Subunit Diameter** 3 mm | 0.118 in

**Diameter Over Jacket** 15 mm | 0.591 in

Mechanical Specifications

Minimum Bend Radius, loaded226 mm8.898 inMinimum Bend Radius, unloaded150 mm5.906 inTensile Load, long term, maximum400 N89.924 lbfTensile Load, short term, maximum1335 N300.12 lbf

Page 4 of 8



# 760251061 | N-144-MP-5K-F16AQ/30T/B2

**Compression** 10 N/mm | 57.101 lb/in

**Compression Test Method** FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

FIEX Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 188 m | 616.798 ft

**Optical Specifications** 

Fiber Type OM4, LazrSPEED® 550

## **Environmental Specifications**

Installation temperature 0 °C to +50 °C (+32 °F to +122 °F)

**Operating Temperature** 0 °C to +60 °C (+32 °F to +140 °F)

**Storage Temperature**  $-40 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

**EN50575 CPR Cable EuroClass Fire Performance** B2ca

**EN50575 CPR Cable EuroClass Smoke Rating** s1a

EN50575 CPR Cable EuroClass Droplets Rating d2

EN50575 CPR Cable EuroClass Acidity Rating a1

**Environmental Space** Low Smoke Zero Halogen (LSZH)

Flame Test Method IEC 60754-2 | IEC 61034-2

## **Environmental Test Specifications**

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $0 \, ^{\circ}\text{C to } +70 \, ^{\circ}\text{C (} +32 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F)}$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$ 



# 760251061 | N-144-MP-5K-F16AQ/30T/B2

**Temperature Cycle Test Method** 

FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 194 kg/km | 130.362 lb/kft

\* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



## 860659158



Fiber Optic Connector Kit, multimode, OM3/OM4, MPO-16/APC, ULL, pinned, green, for 3 mm cable

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

PortfolioCommScope®Product TypeFiber connectorProduct BrandLazrSPEED®

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Male

Interface FeaturePinnedTotal Fiber Count16

**Dimensions** 

Length60.1 mm | 2.366 inCompatible Cable Diameter3 mm | 0.118 in

Material Specifications

Ferrule Material Polymer

Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 ^{\circ}$ 

**Optical Specifications** 

Fiber ModeMultimodeFiber TypeOM3 | OM4

**Insertion Loss Change, mating** 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

**COMMSCOPE®** 

## 860659158

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.2 dB

### Packaging and Weights

Packaging quantity 1

## Regulatory Compliance/Certifications

### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



### \* Footnotes

**Insertion Loss Change, mating**TIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

