

# MLOC5-LS2BNHMW-3M



HELIAX® M-LOC Multiport cluster 5 ports SureFlex® cable assembly with interface type M-LOC latching male to 4.3-10 male, size 3/8", length 3 meters, covered by conduit shield

- WARNING: DO NOT MATE WITH 4.1-9.5 DIN

## Product Classification

<b>Product Type</b>	HELIAX® MLOC cluster, SureFlex® D-CLASS, dynamic PIM
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	MLOC

## General Specifications

<b>Attachment, Connector A</b>	Factory attached
<b>Attachment, Connector B</b>	Factory attached
<b>Body Style, Connector A</b>	Straight
<b>Body Style, Connector B</b>	Straight
<b>Interface, Connector A</b>	M-LOC Male
<b>Interface, Connector B</b>	4.3-10 Male
<b>Specification Sheet Revision Level</b>	B

## Dimensions

<b>Length</b>	3 m   9.843 ft
<b>Nominal Size</b>	3/8 in

## Port Configuration

HOUSING PORT NUMBER	PORT LABEL TEXT			
	STANDARD	"C"	"E"	"N"
1	CL+	CR-	D	ANT 6
2	L-	CL-	A	ANT 1
3	L+	L-	C	ANT 5
4	CL-	R-	B	ANT 2

## Electrical Specifications

<b>3rd Order IMD Dynamic</b>	-119 dBm
------------------------------	----------

# MLOC5-LS2BNHMW-3M

---

**3rd Order IMD Dynamic Test Method**

Two +43 dBm carriers per IEC 62037

## VSWR/Return Loss

<b>Frequency Band</b>	<b>Gated VSWR</b>	<b>Gated Return Loss (dB)</b>	<b>Insertion Loss, typical (dB)</b>
<b>1000–3000 MHz</b>	1.074	29	0.76
<b>3100–4200 MHz</b>	1.074	29	0.91
<b>4200–5000 MHz</b>	1.083	28	1.01

## Mechanical Specifications

**Minimum Bend Radius, multiple Bends** 100 mm | 3.937 in

**Minimum Bend Radius, single Bend** 50 mm | 1.969 in

## Environmental Specifications

**Installation temperature** -40 °C to +60 °C (-40 °F to +140 °F)

**Operating Temperature** -55 °C to +85 °C (-67 °F to +185 °F)

**Storage Temperature** -55 °C to +85 °C (-67 °F to +185 °F)

**Weatherproofing Method** Weatherproofing tube