## U3VQVUCTF

#### **Base Product**



Ultra Low Loss (ULL) OM5 MPO8 APC (Non-Pinned) to Unconnectorized, Fiber Trunk Cable Assembly, 24-Fiber, LSZH B2ca

#### **Product Classification**

Regional Availability Europe

Portfolio CommScope®

 Product Type
 Fiber trunk cable assembly

 Product Brand
 Propel | SYSTIMAX ULL

Ordering Note For additional jacket colors, please contact a CommScope Sales

Green

Representative | For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length may vary based on cable configuration

### General Specifications

Connector A, quantity 3

Color, boot A Gray

Connector B, quantity 0

Construction Type Stranded

Furcation Color Lime green

Interface, Connector A MPO-08/APC Female

Interface, Connector BUnterminatedJacket ColorLime green

Polarity Method B Enhanced (ULL)

Fibers per Subunit, quantity 8

Total Fibers, quantity 24

#### **Dimensions**


Color, connector A

Breakout Length22 inCable Assembly Length Range (m)3 - 305Cable Assembly Length Range (ft)10 - 999

COMMSC PE°

## U3VQVUCTF

### Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0  $^{\circ}$  | 4.40 lb @ 90  $^{\circ}$ 

**Optical Specifications** 

**Fiber Mode** Multimode

**Fiber Type** OM5, LazrSPEED®

### **Environmental Specifications**

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**EN50575 CPR Cable EuroClass Fire Performance** B2ca

**Environmental Space** Indoor | Low Smoke Zero Halogen (LSZH)

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



# U3VQVUCTF

#### Included Products

760253108 N-024-MP-5G-F08LM/20T/B2 Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk with 2.0mm Subunits, 24 fiber, Multimode OM5, Gel-free, Meters jacket marking, Lime green jacket color, B2ca Flame rating

860662232

MPO8,ULL,Multimode,FEMALE,APC,GREEN,2 mm



## 760253108 | N-024-MP-5G-F08LM/20T/B2



Fiber indoor cable, LazrSPEED® Low Smoke Zero Halogen Riser MPO Trunk with 2.0mm Subunits, 24 fiber, Multimode OM5, Gel-free, Meters jacket marking, Lime green jacket color, B2ca Flame rating

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series N-MP

### General Specifications

Cable TypeMPO trunk cableConstruction TypeNon-armoredSubunit TypeGel-free

Filler, quantity

Jacket Color Lime green

Jacket MarkingFeetSubunit, quantity3Fibers per Subunit, quantity8Total Fiber Count24


#### **Dimensions**

Buffer Tube/Subunit Diameter2 mm | 0.079 inDiameter Over Jacket7.8 mm | 0.307 in

## Representative Image



## 760253108 | N-024-MP-5G-F08LM/20T/B2



### Mechanical Specifications

Minimum Bend Radius, loaded 116 mm | 4.567 in

Minimum Bend Radius, unloaded 78 mm | 3.071 in

**Tensile Load, long term, maximum** 200 N | 44.962 lbf

**Tensile Load, short term, maximum** 667 N | 149.948 lbf

**Compression** 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 340 m | 1,115.486 ft

**Optical Specifications** 

Fiber Type OM5, LazrSPEED® wideband

### **Environmental Specifications**

Installation temperature  $0 \,^{\circ}\text{C}$  to +60  $^{\circ}\text{C}$  (+32  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Operating Temperature  $0 \,^{\circ}\text{C}$  to +70  $^{\circ}\text{C}$  (+32  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Page 5 of 8



## 760253108 | N-024-MP-5G-F08LM/20T/B2

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

**EN50575 CPR Cable EuroClass Fire Performance** B2ca

**EN50575 CPR Cable EuroClass Smoke Rating** s1a

EN50575 CPR Cable EuroClass Droplets Rating d0

EN50575 CPR Cable EuroClass Acidity Rating a1

Environmental Space Low Smoke Zero Halogen (LSZH)

**Flame Test Method** IEC 60332-3 | IEC 60754-2 | IEC 61034-2

**Environmental Test Specifications** 

**Low High Bend** 0 °C to +70 °C (+32 °F to +158 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 60.1 kg/km | 40.385 lb/kft

\* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



## 860662232



### MPO8,ULL,Multimode,FEMALE,APC,GREEN,2 mm

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type CommScope®

Fiber connector

General Specifications

ColorGreenColor, bootBlackFerrule GeometryAngled

Interface MPO/APC Female

Interface Feature Unpinned

**Dimensions** 

**Compatible Cable Diameter** 2 mm | 0.079 in

**Optical Specifications** 

Fiber ModeMultimodeFiber TypeOM4 | OM5

**Insertion Loss Change, mating** 0.3 dB

**Optical Components Standard** ANSI/TIA-568-C.3

Insertion Loss Change, temperature0.3 dBInsertion Loss, maximum0.2 dBReturn Loss, minimum45 dB

Packaging and Weights

Packaging quantity 1

\* Footnotes

COMMSCOPE®

## 860662232

**Insertion Loss Change, mating**TIA-568: Maximum insertion loss change after 500 matings

**Insertion Loss Change, temperature** Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

**COMMSCOPE®**