

# 2-1716211-2 | C-012-L2-5K-M12BK/40G/GY/FS/B



LazrSPEED® Indoor/Outdoor, 120 min Fire Survival, Low Smoke Zero Halogen (LSZH), Gel-Filled, Central Loose Tube cable. Provides Rodent Resistance.

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber indoor/outdoor cable
<b>Product Series</b>	C-L2

## General Specifications

<b>Armor Type</b>	Corrugated steel
<b>Cable Type</b>	Loose tube
<b>Subunit Type</b>	Gel-filled
<b>Jacket Color</b>	Black
<b>Jacket Marking</b>	Meters
<b>Jacket Marking Method</b>	Inkjet
<b>Jacket Marking Text</b>	COMMSCOPE GB SYSTEM F O CABLE X-1716211-2 INT/EXT FIRE SURVIVAL 12 X 50/125 OM4 [Serial NUMBER] [METRE MARK]
<b>Fibers per Subunit, quantity</b>	12
<b>Total Fiber Count</b>	12

## Dimensions

<b>Cable Length</b>	2000 m   6,561.68 ft
<b>Buffer Tube/Subunit Diameter</b>	4 mm   0.157 in
<b>Diameter Over Jacket</b>	12.7 mm   0.5 in

## Mechanical Specifications

<b>Minimum Bend Radius, loaded</b>	330 mm   12.992 in
<b>Minimum Bend Radius, unloaded</b>	255 mm   10.039 in
<b>Tensile Load, long term, maximum</b>	400 N   89.924 lbf

# 2-1716211-2 | C-012-L2-5K-M12BK/40G/GY/FS/B

<b>Tensile Load, short term, maximum</b>	1400 N   314.733 lbf
<b>Compression</b>	30 N/mm   171.304 lb/in
<b>Compression Test Method</b>	IEC 60794-1 E3
<b>Impact</b>	10 N-m   88.507 in lb
<b>Impact Test Method</b>	IEC 60794-1 E4
<b>Strain</b>	See long and short term tensile loads
<b>Strain Test Method</b>	IEC 60794-1 E1
<b>Twist</b>	5 cycles
<b>Twist Test Method</b>	IEC 60794-1 E7

## Optical Specifications

<b>Fiber Type</b>	OM4, LazrSPEED®
-------------------	-----------------

## Optical Specifications, Wavelength Specific

<b>Attenuation, maximum</b>	1.00 dB/km @ 1,310 nm   3.00 dB/km @ 850 nm
<b>Standards Compliance</b>	TIA-492AAAD (OM4)

## Environmental Specifications

<b>Operating Temperature</b>	-20 °C to +70 °C (-4 °F to +158 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Cable Qualification Standards</b>	EN 187105   IEC 60794-1-2
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	B2ca
<b>EN50575 CPR Cable EuroClass Smoke Rating</b>	s1b
<b>EN50575 CPR Cable EuroClass Droplets Rating</b>	d0
<b>EN50575 CPR Cable EuroClass Acidity Rating</b>	a1
<b>Environmental Space</b>	Aerial, lashed   Buried   Universal Low Smoke Zero Halogen (ULSZH)
<b>Flame Test Listing</b>	EN 50399   IEC 60332-1-2
<b>Flame Test Method</b>	IEC 60331-25 (120) Fire resistance: 120 minutes at 750 °C (no fiber break)   IEC 60332-1-2
<b>Jacket UV Resistance</b>	UV stabilized
<b>Water Penetration</b>	24 h
<b>Water Penetration Test Method</b>	IEC 60794-1 F5

## Environmental Test Specifications

# 2-1716211-2 | C-012-L2-5K-M12BK/40G/GY/FS/B

---

<b>Low High Bend Test Method</b>	IEC 60794-1 E11
<b>Temperature Cycle</b>	-25 °C to +70 °C (-13 °F to +158 °F)
<b>Temperature Cycle Test Method</b>	IEC 60794-1 F1

## Packaging and Weights

**Cable weight** 216 kg/km | 145.145 lb/kft

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

CS-5K-LT – LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable