


# MLOC4-RGXF-1M



HELIAX® M-LOC Multiport cluster 4 ports SureFlex® cable assembly with interface type M-LOC female to open end, size 0.141", length 1 meter

## Product Classification

<b>Product Type</b>	HELIAX® MLOC cluster, SureFlex® D-CLASS, dynamic PIM
<b>Product Brand</b>	HELIAX®   SureFlex®
<b>Product Series</b>	MLOC

## General Specifications

<b>Attachment, Connector A</b>	Factory attached
<b>Body Style, Connector A</b>	Straight
<b>Interface, Connector A</b>	M-LOC Female
<b>Specification Sheet Revision Level</b>	A

## Dimensions

<b>Length</b>	1 m   3.281 ft
<b>Nominal Size</b>	0.141 in

## Electrical Specifications

<b>3rd Order IMD Dynamic</b>	-119 dBm
<b>3rd Order IMD Dynamic Test Method</b>	Two +43 dBm carriers per IEC 62037

## VSWR/Return Loss

Frequency Band	Gated VSWR	Gated Return Loss (dB)
1000–3000 MHz	1.065	30
3000–4200 MHz	1.106	26
4200–5000 MHz	1.119	25

## Mechanical Specifications

<b>Minimum Bend Radius, multiple Bends</b>	40 mm   1.575 in
--	------------------

# MLOC4-RGXF-1M

---

**Minimum Bend Radius, single Bend**

8 mm | 0.315 in

## Environmental Specifications

**Installation temperature**

-55 °C to +85 °C (-67 °F to +185 °F)

**Operating Temperature**

-55 °C to +85 °C (-67 °F to +185 °F)

**Storage Temperature**

-55 °C to +85 °C (-67 °F to +185 °F)

**Immersion Test Method**

Meets IEC 60529:2001, IP68 in mated condition