
884061804/10 | CS41Z3 BLU C6A 4/24 U/UTP RL 305M ANATEL



CS41Z3, ETL Verified Category 6A U/UTP Cable, low smoke zero halogen, blue jacket, 4 pair count, 1000 ft (305 m) length reel

Product Classification

Regional Availability

Asia | Australia/New Zealand

Portfolio NETCONNECT®

Product Type Twisted pair cable

Country Specific for Brazil

General Specifications

Product Number CS41Z3

ANSI/TIA Category 6A

Cable Component Type Horizontal

Cable Type U/UTP (unshielded)

Conductor Type, singlesSolidConductors, quantity8Jacket ColorBluePairs, quantity4

Separator Type Isolator

Transmission Standards ANSI/TIA-568.2-D | IEC 61156-5

Dimensions


Cable Length304.8 m | 1000 ftDiameter Over Insulated Conductor1.08 mm | 0.043 inDiameter Over Jacket, nominal6.985 mm | 0.275 inJacket Thickness0.508 mm | 0.02 in

Conductor Gauge, singles 24 AWG



884061804/10 | CS41Z3 BLU C6A 4/24 U/UTP RL 305M ANATEL

Cross Section Drawing



Electrical Specifications

dc Resistance Unbalance, maximum 4 %

dc Resistance, maximum 8 ohms/100 m | 2.438 ohms/100 ft

Delay Skew, maximum 45 ns

Dielectric Strength, minimum1500 Vac | 2500 VdcMutual Capacitance at Frequency5.6 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 67 %

Operating Frequency, maximum500 MHzOperating Voltage, maximum80 V

Remote Powering Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the

safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2,

CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Safety Voltage Rating 300 V

Segregation Class



884061804/10 | CS41Z3 BLU C6A 4/24 U/UTP RL 305M ANATEL

Flectrical Cable Performance

CS CommScope

STD Refers to the standard value listed under Transmission Standards in the Electrical Specifications above

TYP Typical Electrical Performance

IL Insertion Loss (dB/100m) NEXT Near End Crosstalk (dB/100m)

 ACR
 Attenuation to Crosstalk Ratio (dB/100m)
 PSNEXT
 Power Sum Near End Crosstalk (db/100m)

 PSACR
 Power Sum Attenuation to Crosstalk Ratio (dB/100m)
 ACRF
 Attenuation to Crosstalk Ratio - Far End (dB/100m)

PSACRF Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m) RL Return Loss (dB)

TCL Transverse Conversion Loss (dB/100m) ELTCTL Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL STD	NEXT STD	ACR STD	PSNEXT STD	PSACR STD	ACRF STD	PSACRF STD	RL
4	3.8	66.3	62.5	63.3	59.5	55.9	53	23
8	5.3	61.7	56.4	58.7	53.4	49.9	46.9	24.5
10	5.9	60.3	54.4	57.3	51.4	48	45	25
16	7.5	57.2	49.7	54.2	46.7	43.9	40.9	25
20	8.4	55.8	47.4	52.8	44.4	42	39	25
25	9.4	54.3	44.9	51.3	41.9	40	37	24.3
31.25	10.5	52.9	42.4	49.9	39.4	38.1	35.1	23.6
62.5	15	48.4	33.4	45.4	30.4	32.1	29.1	21.5
100	19.1	45.3	26.2	42.3	23.2	28	25	20.1
155	24.1	42.4	18.3	39.4	15.3	24.2	21.2	18.8
200	27.6	40.8	13.2	37.8	10.2	22	19	18
250	31.1	39.3	8.3	36.3	5.3	20	17	17.3
300	34.3	38.1	3.9	35.1	0.9	18.4	15.5	16.8
350	37.2	37.1	-0.1	34.1	-3.1	17.1	14.1	16.3
400	40.1	36.3	-3.8	33.3	-6.8	15.9	13	15.9
500	45.3	34.8	-10.5	31.8	-13.5	14	11	15.2

Material Specifications

Conductor MaterialBare copperInsulation MaterialPolyolefin

Jacket Material Low Smoke Fire Retardant Zero Halogen (LSFRZH)

Separator Material Polyolefin

Tape Material Poly/Aluminum/Poly

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

Environmental Specifications



884061804/10 | CS41Z3 BLU C6A 4/24 U/UTP RL 305M ANATEL

Installation temperature $0 \,^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (+32 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Operating Temperature $-20 \,^{\circ}\text{C}$ to +60 $^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Acid Gas Test Method IEC 60754-2

Environmental SpaceLow Smoke Zero Halogen (LSZH)Flame Test MethodIEC 60332-1 | IEC 60332-3-22

Smoke Test Method IEC 61034-2

Packaging and Weights

Cable weight 44.451 kg/km | 29.87 lb/kft

Packaging Type Reel