# L4NR-F




#### N Male Right Angle for 1/2 in LDF4-50A cable

Product Type	Wireless and radiating connector	
Product Brand	HELIAX®	
Product Series	LDF4-50A	
Ordering Note	ANDREW® standard product (Global)	
Warranty	Five years	
General Specifications		
Body Style	Right angle	
Cable Family	LDF4-50A	
Inner Contact Attachment Method	Captivated	
Inner Contact Plating	Silver	
Interface	N Male	
Outer Contact Attachment Method	Clamp	
Outer Contact Plating	Trimetal	
Dimensions		
Length	66.7 mm   2.626 in	
Right Angle Length	39.2 mm   1.543 in	
Diameter	23 mm   0.906 in	
Nominal Size	1/2 in	

## Outline Drawing

Page 1 of 4





#### **Electrical Specifications**

3rd Order IMD	-159 dBc
3rd Order IMD at Frequency	-116 dBm @ 900 MHz
3rd Order IMD Test Method	Two +43 dBm carriers
Insertion Loss Coefficient, typical	0.05
Average Power at Frequency	0.6 kW @ 900 MHz
Connector Impedance	50 ohm
dc Test Voltage	2000 V
Impedance	50 ohm
Inner Contact Resistance, maximum	1 mOhm
Insulation Resistance, minimum	5000 MOhm
Operating Frequency Band	0 – 8800 MHz
Outer Contact Resistance, maximum	0.25 mOhm
RF Operating Voltage, maximum (vrms)	707 V

Page 2 of 4



# L4NR-F

### VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)	Gated VSWR	Gated Return Loss (dB)	VSWR, typical	Return Loss, typical (dB)
0–1000 MHz	1.05	32.26	1.023	39		
1000-2200 MHz	1.119	25	1.074	29		
2200-3000 MHz	1.15	23.12	1.106	26		
2700-3600 MHz	1.15	23.12	1.106	26		
3600-5000 MHz	1.22	20.07	1.106	26		
5000-6000 MHz	1.33	16.97	1.152	23		
6000-8800 MHz			1.253	19	1.501	13.97

#### Mechanical Specifications

Attachment Durability	25 cycles
Connector Retention Tensile Force	600 N   134.885 lbf
Connector Retention Torque	4.5 N-m   39.828 in lb
Coupling Nut Proof Torque	1.7 N-m   15.046 in lb
Coupling Nut Retention Force	450 N   101.164 lbf
Coupling Nut Retention Force Method	MIL-C-39012C-3.25, 4.6.22
Interface Durability	500 cycles
Interface Durability Method	IEC 61169-16:9.5
Mechanical Shock Test Method	IEC 60068-2-27

#### **Environmental Specifications**

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Corrosion Test Method	IEC 60068-2-11
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68
Thermal Shock Test Method	IEC 60068-2-14
Vibration Test Method	IEC 60068-2-6

#### Packaging and Weights

Page 3 of 4



# L4NR-F

Height, packed	248.92 mm   9.8 in
Width, packed	266.7 mm   10.5 in
Length, packed	266.7 mm   10.5 in
Packaging quantity	50

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



### \* Footnotes

Warranty	For more information, please consult our Product Warranty guidelines
Insertion Loss Coefficient, typical	$0.05\sqrt{-1}$ freq (GHz) (not applicable for elliptical waveguide)
Immersion Depth	Immersion at specified depth for 24 hours



